




MODULAR WALL PLATES & JACKS

110 TYPE MOUNTING BLOCKS, SINGLE & DOUBLE JACK

- Single Jack, Screw-on Cover
- Comes w/ Double Sided Sticker and Mounting Screws
- Gold Plated Contacts
- 110 Type IDC Termination with 2 Pair Caps
- Wiring: 6P4C & 6P6C -- USOC 8P8C -- AT&T



PT-1103-6C

PT-1103-4C	RJ11, 4C
PT-1103-6C	RJ11, 6C
PT-1103-6DEC	DEC Type Jack
PT-1103-8C	RJ45 Regular
PT-1103-8CK	RJKeyed

PT-1103-4/UL	RJ11, 4C
PT-1103-6/UL	RJ11, 6C
PT-1103-6DEC/UL	Dec Type Jack
PT-1103-8/UL	RJ45 Regular
PT-1103-8K/UL	RJ45 Keyed



- Double Jack, Screw-on Cover
- Comes w/ Double Sided Sticker & Mounting Screws
- Gold Plated Contacts
- 110 Type IDC Termination with 2 Pair Caps



PT-1104B-88

PT-1104B-44	2 RJ11, 4C
PT-1104B-66	2 RJ11, 6C
PT-1104B-6DD	IDC6DEC Dual Surf.
PT-1104B-88	2 RJ45, Regular
PT-1104B-88K	2 RJ45, One Keyed Port
PT-1104B-8KK	2 RJ45, Dual Keyed Port

PT-1104B-44/UL	2 RJ11, 4C
PT-1104B-66/UL	2 RJ11, 6C
PT-1104B-68K/UL	1 RJ11, 1RJ45 Keyed
PT-1104B-88/UL	2 RJ45, Regular
PT-1104B-88K/UL	2 RJ45,
PT-1104B-6DD/UL	One Keyed Port 2 DEC Type
PT-1104B-66D/UL	Dual Port



110 TYPE SINGLE WALL JACKS

- Single Jack Plastic Fittings for **PT-113C-UL** Wall Plates
- UL Listed, Gold Plated Contacts
- 110 Type Termination
- Wiring: 6P4C & 6P6C -- USOC 8P8C -- AT&T
- Copy of wiring code included

PT-113-4C-UL	6P4C, USOC
PT-113-6C-UL	6P6C, USOC
PT-113-6D-UL	6 DEC Type
PT-113-8C-UL	8P8C, AT&T
PT-113-8CK-UL	8P8C Keyed, AT&T



PT-113-4C-UL

110 TYPE DUAL WALL JACK

- Double Jack Plastic Fitting for **PT-114C-UL** Wall Plates
- UL Listed, Gold Plated Contacts
- 110 Type Termination
- Wiring: 6P4C & 6P6C -- USOC 8P8C -- AT&T



PT-114-44-UL	2 6P4C, USOC
PT-114-66-UL	2 6P6C, USOC
PT-114-6DD-UL	2 6-DEC Type
PT-114-68K-UL	1 6P6C Voice, 1 8P8C, AT&T
PT-114-88-UL	2 8P8C, AT&T
PT-114-88K-UL	1 8P8C Voice, 1 8P8C Data Both AT&T
PT-114-8KK-UL	2 8P8C Keyed, AT&T




PT-114-44-UL

PLASTIC WALL PLATES

- Single or Dual Hole, Single Gang Wall Plates
- UL Listed, copy of wiring code included
- Single Gang Box or PT-115BUL Type Box



PT-113C-UL	Single Hole Wall Plate
PT-114C-UL	Dual Hole Wall Plate



PT-113C-UL

PLASTIC WALL BOXES

- For Single, Dual Hole or Any Single Gang Wall Plates
- UL Listed
- Three different depth for different fitting, See Figures Below
- Use PT-115B Boxes for PT-113 and PT-114 type jacks



PT-115-UL	Ivory, 7/8" Deep
PT-115B-UL-IV	Ivory, 1 3/4" Deep
PT-115B-UL-WH	White, 1 3/4" Deep



PT-115-UL