




MARKING:

QUEST CABLING SOLUTIONS 350MHz (UL) E305668 TYPE CM 24AWG 75°C CSA 204790 CM 75°C

ETL VERIFIED TIA/EIA-568B.2 UTP CAT5E RoHS COMPLIANCE BATCH NO.

8244-3	
P1	P2
1	3
2	6
3	1
6	2
4	4
5	5
7	7
8	8
WHITE/ORANGE	
ORANGE	
WHITE/GREEN	
GREEN	
BLUE	
WHITE/BLUE	
WHITE/BROWN	
BROWN	

*NOTE: All relevant materials are complied with RoHS directive .

3	MOLDED PVC SEE LIST	H1BP01-0304	M304
2	4 TWISTED PAIRS CAT.5E 24AWG(7/0.19AS) UTP, OD 5.3mm, JACKET SEE LIST, DRAWING No. EU002404P-429		L+20mm M304
1	8P8C MODULAR PLUG, GOLD PLATING 3u" ON CONTACTS	A1ND30-0205	2 M205
No.	DESCRIPTION		Q'TY Supplier
APPROVED	QUEST TECHNOLOGY INTERNATIONAL, Inc. Quest Technology Int'l, Inc. 11200 NW 138th St, Medley, FL 33178		
CHECKED			
DRAWING			
DATE			
20/AUG/13	ITEM NO.	NPC-2XXXX	UNIT:mm
			±10mm ±20mm ±25mm ±30mm ±40mm
			0 ~200mm 201~1000mm 1001 ~1500mm 1501~2100mm 2100mm↑
			Unless Other Spec. Tolerances:

ITEM NO.	LENGTH (FT)
NPC-2X01	1
NPC-2X02	2
NPC-2X03	3
NPC-2X05	5
NPC-2X07	7
NPC-2X10	10
NPC-2X15	15
NPC-2X25	25
NPC-2X50	50
NPC-2X75	75
NPC-2X00	100

NPC-2XXX

LENGTH

COLOR CODE

JACKET COLOR & PVC COLOR	COLOR CODE
BLACK	1
BLUE	2
RED	3
ORANGE	4
YELLOW	5
GREEN	6
WHITE	8
GREY	9

PACKING: 1PC IN A POLYBAG



WHITE CABLE TIE



*NOTE: All relevant materials are complied with RoHS directive.

APPROVED		 QUEST Technology Int'l, Inc. 11200 NW 138th St., Medley, FL 33178		Cable Length Unless Other Spec. Tolerances:
CHECKED	HU			
DRAWING	JIANG			
DATE	20/AUG/13	ITEM NO.	NPC-2XXX	UNIT:mm
				 