



## 101A073-3-0 Product Details

[Share](#) | [Print](#) | [Email](#)


**101A073-3-0**

TE Internal Number: 843056-000

Active

### Molded Parts

Always EU RoHS/ELV Compliant (Statement of Compliance)

### Product Highlights:

- Molded Part Type = End Cap
- Family Name = 101A0
- General Purpose Application
- 3 Material Code
- Adhesive Code = S1017, S1048

[View all Features](#)

### Quick Links

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#)
[Request Sample](#)
[Find Similar Products](#)
[Buy Product](#)

### Documentation & Additional Information

#### Product Drawings:

- [Cap, Round End \(PDF, English\)](#)

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files:

- None Available

#### Additional Information:

- [Product Line Information](#)

#### Related Products:

- [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- Molded Part Type = End Cap
- Family Name = 101A0
- Adhesive Description = Adhesive Purchased Separately.
- Size = 73

#### Mechanical Attachment:

- Adhesive Pre-Coating = Without

#### Dimensions:

- Length (M [ft]) = 0.091 [0.30]
- Expanded ID, Min. (mm [in]) = 39.40 [1.561]
- Recovered ID, Max. (mm [in]) = 18.00 [0.710]

#### Body Features:

- Wall Thickness - Full Recovery (Nominal) (mm [in]) = 2.54 [0.100]
- Material = Semi rigid Modified Polyolefin

#### Configuration Features:

- Material Code = 3

#### Industry Standards:

- Government/Industry Qualification = No
- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

#### Operation/Application:

- Application = General Purpose

#### Purchasing Information:

- Adhesive Code = S1017, S1048

#### Other:

- Brand = Raychem

### Corporate Information

[About TE](#)  
[Investors](#)  
[News Room](#)  
[Supplier Portal](#)  
[Careers](#)  
[Terms & Conditions](#)  
[Privacy Policy](#)

### Quick Links

[Distributor Inventory](#)  
[Product Cross Reference](#)  
[Documents & Drawings](#)  
[Product Compliance Support Center](#)  
[Site Map](#)

### Customer Support

[Email or Chat With Us](#)  
[Find a Phone Number](#)  
[Knowledge Base](#)  
[Manage Your Account](#)

### Keep Me Informed

