

New



ITEM #

DESCRIPTION

TSK-1180 51 PC. ELECTROMECHANICAL TOOL KIT

CONTAINS:

- 3 1/2 DIGITAL MULTIMETER • 30 WATT SOLDERING IRON
- DESOLDERING PUMP • SOLDERING IRON STAND
- SOLDER TUBE • 3 PC. SOLDERING AID KIT • BRUSH
- 5" FLAT NOSE PLIERS • 5" NEEDLE NOSE PLIERS
- 5" BENT NEEDLE NOSE PLIERS • 4.5" SIDE CUTTERS
- 6" ADJUSTABLE WRENCH • 6" STAINLESS STEEL SCISSORS
- 6" LONG TWEEZERS • 7 PC. FOLDING HEX KEY WRENCH
- 2 PC. NEEDLE FILE SET (ROUND & FLAT) • UTILITY KNIFE
- 10 PC. SCREWDRIVER SET: PHILLIPS SCREWDRIVERS: #0x75, #1x75, #2x100, #2x38mm, SLOTTED SCREWDRIVERS: 3.2x75, 5x75, 6x100, 5x150, 6x150mm • PRECISION SCREWDRIVER SET: PHILLIPS: #0, #1, SLOTTED: 1.0, 1.6, 2.4, 3.0mm • 10FT. TAPE MEASURE
- PVC ELECTRICAL TAPE • COMPONENTS STORAGE BOX
- 2x MULTI-POCKET REMOVABLE PALLETES
- ATTACHE STYLE TOOL CASE: 17.5" x 12.6" x 3.3"



ITEM #

DESCRIPTION

TPK-6000 85 PC. FIELD SERVICE TOOL KIT

CONTAINS:

- 3 1/2 DIGITAL MULTIMETER • CONTINUITY TESTER
- 34 PC. CORDLESS SCREWDRIVER (CHARGER, 33 BITS, CASE)
- DELUXE MINI TORCH • 30 WATT SOLDERING IRON
- DESOLDERING PUMP • SOLDERING IRON STAND
- TELESCOPIC INSPECTION MIRROR
- 3 PC. SOLDERING AID KIT • 6" ADJUSTABLE WRENCH
- 5 1/4" LONG NOSE PLIERS • 4 1/2" DIAGONAL CUTTER
- 5 1/4" FLAT NOSE PLIERS • 6 1/2" STAINLESS SCISSORS
- 5 1/4" BENT NOSE PLIERS • 8 1/2" WIRE CRIMPER/STRIPPER
- 7 PC. FOLDING HEX KEY WRENCH • TWEEZERS • 5 PC. NEEDLE FILE SET • SNAP-OFF BLADE CUTTER • CLAMP VISE
- ALIGNMENT SCREWDRIVER • SURE-GRIP SCREWDRIVER SET: PHILLIPS SCREWDRIVERS: #0x3.2mmx3", #1x5mmx4", #2x6mmx4", #2x6mmx1.5", #3x8mmx6", SLOTTED SCREWDRIVERS: 3.2mmx3", 5mmx4", 6mmx4", 8mmx6", 6mmx1.5"
- 6 PC. SCREWDRIVER SET: PHILLIPS: #0, #1, SLOTTED: 1.4, 2.0, 2.4, 3.0mm • PVC ELECTRICAL TAPE • TAPE MEASURE
- COMPONENTS BOX • ABS MOLDED TOOL CASE: 18.5" x 14.1" x 6.3"

