



Search by part # or keyword

Products

Industries & Solutions

Resources

Shop TE


Sign In



Wire & Cable > Hook Up Wire

22759/32-16-09 ACTIVE

Hook Up Wire, MIL-DTL-22759, 600V Hook Up Wire Voltage Rating, 16AWG Wire Size, White Hook Up Wire Wire Color



Raychem

TE Internal #: **EG3491-000**

TE Internal Description: **22759/32-16-09**

Mil-Spec: **M22759/32-16-09**

Hook Up Wire Cable Type : **MIL-DTL-22759**

Hook Up Wire Voltage Rating (V): **600**

Hook Up Wire Insulation Material : **Modified Radiation Cross-linked ETFE Polymer**

Hook Up Wire Conductor Material : **Tin-Coated Copper**

Hook Up Wire Wire Color : **White**

[Add to List](#) | [Digital Datasheet](#)

[Compatible Parts & Tooling](#)

SHOP OUR DISTRIBUTORS

North America

We are here to help!

Get in touch with our product experts.

[CHAT WITH US](#)

[EMAIL US](#)

[CALL US](#)

Documents

Features

Product Compliance

Product Drawings

Wire, Radiation-Crosslinked, Modified, ETFE-Insulated, Tin-Coated Copper, Lightweight
tif English

Dimensional Drawing

22759/32-16-09

[22759/32-16-09](#)

English

Datasheets & Catalog Pages

1654025_Sec9_SPEC55

[ENG_CS_1654025_Sec9_SPEC55_0313.pdf](#)

English

Raychem Wire and Cable Quick Reference Guide

[ENG_DS_1-1773735-6_1116.pdf](#)

English

Product Specifications

Product Specification

[ENG_SS_SPEC55A_4.pdf](#)

English

Compatible Parts

Filter By Specification



ASSOCIATED

650076-000

Splices, Splice, Splice, 16 – 12AWG Wire Size, 1.21 – 2.94mm² Wire...

From: \$3.710

In-Stock

[ADD TO CART](#)


Customers Also Bought



TE Part #: **H81K11BAA**

Holsworthy Holco, Through-Hole Resistors, Precision...

[View Product](#)



TE Part #: **3-87962-1**

PCB Mount Receptacle, Right Angle, Board-to-Board, 64...

[View Product](#)



TE Part #: **44A0211-8-9**

Hook Up Wire, Spec 44, 1000V Hook Up Wire...

[View Product](#)



TE Part #: **55A0812-22-0**

Hook Up Wire, Spec 55, 600V Hook Up Wire...

[View Product](#)