




## 224W221-25/225-0 Product Details

[Share](#) | [Print](#) | [Email](#)


Active

### Molded Parts

224W221-25/225-0

**224W221-25/225-0**

TE Internal Number: 031172-000

#### Product Highlights [View All](#)

- VG95343 Parts 6,7,8 and 9
- Molded Part Type = Molded Boot
- Molded Part Shape = 90°
- Molded Part Lip = With Lip
- Operating Temperature = -75 - 150 °C

[Pricing & Availability](#)
[Request Sample](#)
[Add to My Part List](#)
[Buy Product through Distributor](#)
[Documents](#) | [Features](#) | [Compliance](#)

#### Please Note:

Use the Product Drawing for all design activity

#### Product Type Features

Molded Part Type	Molded Boot
Molded Part Shape	90°
Molded Part Lip	With Lip
Angle	90°
Adhesive Description	Unicure Pre-Coated Epoxy Adhesive
Size	21
Family Name	224W2
Color	Black

#### Mechanical Attachment

Adhesive Pre-Coating	With
----------------------	------

#### Dimensions

Cable Diameter Range (mm [in])	9.40 - 11.00 [0.370 - 0.430]
Expanded ID, Min. (mm [in])	11.00 [0.430]
Recovered ID, Max. (mm [in])	9.40 [0.370]

#### Body Features

Material	Fluid Resistant Modified Elastomer
----------	------------------------------------

#### Housing Features

Material Systems Code	25
Max. Inside Diameter of Part (mm [in])	9.40 [0.370]

#### Configuration Features

Material Code	25
---------------	----

#### Industry Standards

Government/Industry Qualification	No
-----------------------------------	----

Approved Standards	VG95343 Parts 6,7,8 and 9
--------------------	---------------------------

RoHS/ELV Compliance	RoHS compliant, ELV compliant
---------------------	-------------------------------

Lead Free Solder Processes	Not relevant for lead free process
----------------------------	------------------------------------

RoHS/ELV Compliance History	Always was RoHS compliant
-----------------------------	---------------------------

#### Environmental

Operating Temperature (°C)	-75 - +150
----------------------------	------------

#### Operation/Application

Application	General Purpose
-------------	-----------------

#### Purchasing Information

Adhesive Code	225
---------------	-----

#### Other

Brand	Raychem
-------	---------

#### Related Products

Not quite the product you're looking for?

[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)

Feedback

#### Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms of Use of TE.com](#)
- [Privacy Policy](#)
- [Global Accessibility Statement](#)

#### Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)
- [Terms & Conditions of Sale](#)

#### Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

#### Keep Me Informed

