









T OPTION
PROVIDES CUTOUTS IN ORDER TO
ACCOMMODATE TABS




PUSH FIT RFI COMB
(SILVER PLATED BRASS)
COMB SUPPLIED SEPARATELY

HARDWARE OPTIONS


CODE: (NO CODE)
STANDARD
SLOTTED
HEAD SCREW




CODE: SSL
SHORT
SLOTTED
HEAD SCREW




CODE: H
HEX SOCKET
HEAD SCREW



CODE: E
EXTENDED
SCREW




CODE: PF
JACK POST
(4-40 UNC)




WASHERS
WASHERS
SHOWN FOR
REFERENCE
ONLY

CODE: PF-0
THREADED
HOLE
4-40 UNC




4-40UNC - 2B
NOT
SUPPLIED
WITH
HARDWARE

CODE: M3-0
THREADED
HOLE
M3



M3x0.5 - 6H
NOT
SUPPLIED
WITH
HARDWARE

ORDERS CANNOT BE PLACED AGAINST ALPHA ISSUED DRAWINGS.
ON RECEIPT OF CUSTOMER APPROVAL, THE DRAWING STATUS WILL BE RAISED TO ISSUE 1.

DRAWN	DIW		DATE 04/08/2016		3RD ANGLE PROJECTION NOT TO SCALE	PART NUMBER: D**-1-BT**-**					 Polamco 		
SALES APPR			04/08/2016			TITLE: D-SUB BANDING BACKSHELL							
DESIGN APPR	K. SHEPPARD	02/03/2016	UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS IN MILLIMETRES GENERAL TOL LINEAR +/- 0,25MM ANGULAR +/- 1°		ASSY USED ON: MIL-DTL-24308								
PROD APPR													
QUAL APPR				MATERIAL SEE PART NUMBER BREAKDOWN FINISH SEE PART NUMBER BREAKDOWN		THIS DRAWING IS COPYRIGHT AND THE PROPERTY OF POLAMCO LTD IT MUST NOT BE COPIED, USED FOR MANUFACTURE OR OTHERWISE DISCLOSED WITHOUT PRIOR WRITTEN CONSENT OF THE COMPANY.					POLAMCO LTD, WESTON LOCK, LOWER BRISTOL ROAD BATH BA2 1EP	SHT 1	DRAWING NO: P10143
ISSUE	REV.	DCR											
10	2	5821											
NCAGE CODE U5792			WEIGHT ---										

D25-1-BT-08E-1-C-T-L20-E

CONNECTOR TYPE _____
SHELL SIZE (SEE TABLE 1) _____
INSERT H FOR RFI COMB COMPATABILITY _____
ENTRY POSITION (TOP ENTRY) _____
TERMINATION STYLE _____
(BT - BAND TERMINATION STYLE)
ENTRY SIZE (SEE TABLE 2) _____
INSERT E FOR ELLIPTICAL ENTRY _____
ENTRY SIZES 07 AND ABOVE ONLY
OMIT FOR STANDARD CIRCULAR ENTRY
MATERIAL (TABLE 3) _____
PLATING (TABLE 3) _____
T OPTION _____
OMIT FOR STANDARD FLANGE
OPTIONAL LENGTH (5MM INCREMENTS) _____
(OMIT FOR STANDARD LENGTH, STANDARD LENGTH = 30MM)
HARDWARE OPTION _____
OMIT FOR STANDARD

TABLE 1

SHELL SIZE	MIL SPEC SHELL SIZE REFERENCE	A	B	C	D	MAX ENTRY (CIRCULAR)	MAX ENTRY (ELLIPTICAL)
09	1	31,19	25,00	12,93	22,86	06	08E
15	2	39,52	33,33	12,93	31,09	06	10E
25	3	53,42	47,02	12,93	44,86	06	12E
37	4	69,76	63,50	12,93	61,32	06	15E
50	5	67,31	61,12	15,75	58,98	08	16E
104	6	69,70	63,50	17,35	NA	09	18E

TABLE 2A


ENTRY SIZE (CIRCULAR)	G	H MAX
01	3,18	9,00
02	4,75	9,00
03	6,86	11,30
04	7,37	13,10
05	7,92	13,10
06	10,03	13,63
07	10,67	14,27
08	12,70	16,30
09	14,27	17,90

TABLE 2B

ENTRY SIZE (ELLIPTICAL)	E MIN	F MIN	J	EQUIV. CIRCULAR ENTRY DIAMETER
07E	13,0	9,5	16,6	(11,1)
08E	16,5	9,5	20,1	(12,7)
09E	20,5	9,5	24,1	(14,3)
10E	24,7	9,5	28,3	(15,9)
11E	29,4	9,5	33,0	(17,5)
12E	34,6	9,5	38,2	(19,1)
13E	40,2	9,5	43,8	(20,6)
14E	46,2	9,5	49,8	(22,2)
15E	52,7	9,5	56,3	(23,8)
16E	50,0	12,0	53,6	(25,4)
17E	49,2	13,9	52,8	(27,0)
18E	54,9	13,9	58,5	(28,6)

TABLE 3

CODE	MATERIAL / PLATING
1-C	ALUMINIUM / ELECTROLESS NICKEL
1-B	ALUMINIUM / CADMIUM OLIVE DRAB OVER ELECTROLESS NICKEL
1-U	ALUMINIUM / UNPLATED
1-ZB	ALUMINIUM / ZINC COBALT OLIVE DRAB OVER ELECTROLESS NICKEL
1-ZN	ALUMINIUM / ZINC NICKEL BLACK PASSIVATE OVER ELECTROLESS NICKEL
1-Y	ALUMINIUM / YELLOW CHROMATE OVER CADMIUM
4-J	STAINLESS STEEL / PASSIVATE

DRAWN	DIW		DATE 04/08/2016	 3RD ANGLE PROJECTION NOT TO SCALE	PART NUMBER: D**-1-BT-**-**					 Polamco 		
SALES APPR			04/08/2016		TITLE: D-SUB BANDING BACKSHELL							
DESIGN APPR	K. SHEPPARD	02/03/2016	UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS IN MILLIMETRES GENERAL TOL LINEAR +/- 0,25MM ANGULAR +/- 1°									
PROD APPR												
QUAL APPR												
ISSUE	REV.	DCR		MATERIAL SEE PART NUMBER BREAKDOWN	ASSY USED ON:					SHT	DRAWING NO:	
10	2	5821										
NCAGE CODE U5792			WEIGHT ---	FINISH SEE PART NUMBER BREAKDOWN	THIS DRAWING IS COPYRIGHT AND THE PROPERTY OF POLAMCO LTD IT MUST NOT BE COPIED, USED FOR MANUFACTURE OR OTHERWISE DISCLOSED WITHOUT PRIOR WRITTEN CONSENT OF THE COMPANY.					POLAMCO LTD, WESTON LOCK, LOWER BRISTOL ROAD BATH BA2 1EP	2	P10143