




202K142-25-00/225-0 Product Details

[Share](#) | [Print](#) | [Email](#)


Active

Molded Parts

202K142-25-00/225-0

202K142-25-00/225-0

TE Internal Number: 980683-000

Product Highlights [View All](#)

- VG95343 Parts 6,7,8 and 9
- Molded Part Type = Molded Boot
- Molded Part Shape = Straight
- Molded Part Lip = With Lip
- Operating Temperature = -75 - 150 °C

- [Pricing & Availability](#)
- [Request Sample](#)
- [Add to My Part List](#)
- [Buy Product through Distributor](#)

[Documents](#) | [Features](#) | [Compliance](#)

Related Products

Not quite the product you're looking for?

[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)

Feedback

Please Note:
Use the Product Drawing for all design activity

Product Type Features

Molded Part Type	Molded Boot
Molded Part Shape	Straight
Molded Part Lip	With Lip
Angle	180°
Adhesive Description	Unicure Pre-Coated Epoxy Adhesive
Size	42
Family Name	202K1
Color	Black

Configuration Features

Material Code	25
Industry Standards	
Government/Industry Qualification	No
Approved Standards	VG95343 Parts 6,7,8 and 9
RoHS/ELV Compliance	RoHS compliant, ELV compliant
Lead Free Solder Processes	Not relevant for lead free process
RoHS/ELV Compliance History	Always was RoHS compliant

Mechanical Attachment

Adhesive Pre-Coating	With
----------------------	------

Dimensions

Expanded ID, Min. (mm [in])	31.00 [1.220]
Recovered ID, Max. (mm [in])	18.00 [0.710]

Body Features

Material	Fluid Resistant Modified Elastomer
----------	------------------------------------

Housing Features

Material Systems Code	25
Max. Inside Diameter of Part (mm [in])	18.00 [0.710]

Environmental

Operating Temperature (°C)	-75 - +150
----------------------------	------------

Operation/Application

Application	General Purpose
-------------	-----------------

Purchasing Information

Adhesive Code	225
---------------	-----

Other

Brand	Raychem
-------	---------

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)
- [Global Accessibility Statement](#)

Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed

