

## Data sheet

### OpDAT REGpro front cover 3RU, 7HP 6xSC-D SM + MM (ceramic)

P/N  
15024AD206-E


EAN 4250184170792

2017-06-02

## Illustrations



Dimensional drawing



See enlarged drawings at the end of document

## Product specification

- front plate 3RU/7HP with 6 SC-D couplers
- slotted ceramics sleeve for single mode and multimode applications
- suitable for mounting in OpDAT REGpro and OpDAT REGpro24
- gray, powder-coated steel sheet
- front plate 3RU/7HP LC-Q adapters
- slotted ceramics sleeve for single mode and multi mode applications
- suitable for mounting in OpDAT REGpro and OpDAT REGpro24
- gray, powder-coated steel sheet
- variants: 3 or 6 LC-Q (blue), 3 or 6 LC-Q (heather violet), 3 or 6 LC-Q (aqua) or 3 or 6 LC-Q APC (green)

### Technical Data

#### General Data

Fields of application	Structured building cabling
Design	Front cover
Mounting style	3RU/7HP
Transmission technology	Fiber optic
Color	metallike
Dimensions	
Dimension (L x W x H)	28.60 x 128.90 x 35.30 mm
Dimension (L x W x H)	1.126 x 5.075 x 1.39 in.
Height unit	3RU
Horizontal pitch	7Units
Mode type of the fiber	Singlemode + Multimode

#### Connections/interfaces

Connector technology interface 1	SC-D Couplers
Connector technology interface 2	SC-D Couplers
Number of ports interface 1	6
Number of ports interface 2	6
Number of equipped ports interface 1	6
Number of ports interface 2 equipped	6
Number of ports with dust protection interface 1	6
Number of ports with dust protection interface 2	6

#### Mechanical characteristics

Cut-out	SC-D, LC-Q, ST-D
Connector type	Duplex
Life - Number of mating cycles	min. 1000

#### Materials and material properties

Material - Mounting plate	steel
Material - Mounting plate finish	powder-coated
Material - Sleeve	ceramic, slotted
Material - Coupler housing	Plastics



Data sheet

Page 3/4

## OpDAT REGpro front cover 3RU, 7HP 6xSC-D SM + MM (ceramic)

P/N

15024AD206-E

EAN 4250184170792

2017-06-02

### Technical Data

#### Approvals

RoHS	compliant
------	-----------

#### The product meets the following standards

Fibre optic connector interfaces	DIN EN 61754-4
----------------------------------	----------------

#### Classifications

ETIM 5.0	EC001130
----------	----------

ETIM 6.0	EC001130
----------	----------

#### Packing details

Type of packaging	1 pc(s) / plastic bag
-------------------	-----------------------

Packaging unit - Weight (gram)	168.00 g
--------------------------------	----------

Packaging unit - Weight (pound)	0.37 lb
---------------------------------	---------



Illustrations

Dimensional drawing

