



RT-780-1-1/4-3-SP Product Details

[Share](#) [Print](#) [Email](#)


RT-780-1-1/4-3-SP

TE Internal Number: CP4650-000

Active

Heat Shrinkable Tubing for Nuclear Environments

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Packaging Method = Spool
- Without
- Thin Wall Style
- Expanded ID, Min. = 31.75 mm
- Recovered ID, Max. = 15.87 mm

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Color = Orange

Mechanical Attachment:

- [Adhesive Pre-Coating](#) = Without

Electrical Characteristics:

- [Recovered ID, Max. \(mm \[in\]\)](#) = 15.87 [0.625]

Dimensions:

- [Expanded ID, Min. \(mm \[in\]\)](#) = 31.75 [1.250]

Body Features:

- [Wall Style](#) = Thin
- [Wall Thickness-Full Recovery, Min. \(mm \[in\]\)](#) = 0.94 [0.037]
- [Expansion Ratio](#) = 2:1

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- [RoHS/ELV Compliance History](#) = Always was RoHS compliant

Environmental:

- [Operating Temperature Range \(°C\)](#) = -55 - +175

Packaging Features:

- [Packaging Method](#) = Spool

Product Availability:

- [Region](#) = Worldwide
- [Applicable Country](#) = Worldwide

Other:

- [Brand](#) = Raychem

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)

Quick Links

- [Check Distributor Inventory](#)
- [Cross Reference Products](#)
- [Find Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Search Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

[▶](#)

