



## RT-780-5/8-3-SP Product Details

[Share](#) [Print](#) [Email](#)


RT-780-5/8-3-SP

TE Internal Number: CP2529-000

Active

### Heat Shrinkable Tubing for Nuclear Environments

Always EU RoHS/ELV Compliant (Statement of Compliance)

#### Product Highlights:

- Packaging Method = Spool
- Without
- Thin Wall Style
- Expanded ID, Min. = 15.90 mm
- Recovered ID, Max. = 7.95 mm

[View all Features](#)

#### Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

### Documentation & Additional Information

#### Product Drawings:

- None Available

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files:

- None Available

#### Additional Information:

- [Product Line Information](#)

#### Related Products:

- [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- Color = Orange

#### Mechanical Attachment:

- [Adhesive Pre-Coating](#) = Without

#### Electrical Characteristics:

- [Recovered ID, Max. \(mm \[in\]\)](#) = 7.95 [0.312]

#### Dimensions:

- [Expanded ID, Min. \(mm \[in\]\)](#) = 15.90 [0.625]

#### Body Features:

- [Wall Style](#) = Thin
- [Wall Thickness-Full Recovery, Min. \(mm \[in\]\)](#) = 0.58 [0.023]
- [Expansion Ratio](#) = 2:1

#### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- [RoHS/ELV Compliance History](#) = Always was RoHS compliant

#### Environmental:

- [Operating Temperature Range \(°C\)](#) = -55 - +175

#### Packaging Features:

- [Packaging Method](#) = Spool

#### Product Availability:

- [Region](#) = Worldwide
- [Applicable Country](#) = Worldwide

#### Other:

- [Brand](#) = Raychem

### Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)

### Quick Links

- [Check Distributor Inventory](#)
- [Cross Reference Products](#)
- [Find Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

### Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Search Knowledge Base](#)
- [Manage Your Account](#)

### Keep Me Informed

Receive TE News, Events & Technology Updates

[▶](#)

