



AP2000-107-0-60MM Product Details

[Share](#) | [Print](#) | [Email](#)


Active

Heat Shrink Tubing

AP2000-107-0-60MM

AP2000-107-0-60MM

TE Internal Number: CJ0040-000

Product Highlights [View All](#)

- Heat Shrinkable Tubing
- Product Name = AP2000
- Product Source = U.S.
- Semiflexible
- Medium Wall Style

[Pricing & Availability](#)
[Request Sample](#)
[Add to My Part List](#)
[Buy Product through Distributor](#)
[Feedback](#)
[Documents](#)
[Features](#)
[Compliance](#)

Please Note:

Use the Product Drawing for all design activity

Product Type Features

Product Type	Heat Shrinkable Tubing
Color	Black

Dimensions

Expanded ID, Min. (mm [in])	19.00 [0.748]
Recovered ID, Max. (mm [in])	7.40 [0.290]
Cut Length (mm [in])	60.00 [2.360]

Body Features

Product Name	AP2000
Pliancy	Semiflexible
Wall Style	Medium
Wall Type	Dual
Lining Type	Adhesive
Material	Irradated Modified Polyolefin
Shrink Ratio	2.5:1
Fluid Type	Brake Fluid, Unleaded Gasoline
Resistant To	Fluids, Impact

Housing Features

Material Systems	No
------------------	----

Industry Standards

Government/Industry Qualification	No
Flammability Rating	Non-Flame-Retardant
Approved Standards	RW-1001
RoHS/ELV Compliance	RoHS compliant, ELV compliant
Lead Free Solder Processes	Not relevant for lead free process
RoHS/ELV Compliance History	Always was RoHS compliant

Environmental

Fluid Resistance	Immersion
Operating Temperature (°C)	-40 - +80

Conditions for Usage

Full Recovery Temperature (°C)	115
Shrink Temperature, Min. (°C)	110
High Temperature Compatible	No

Operation/Application

Emission Free Type	Halogen-free
Product Use	Brake Pipe Protection
Application	Automotive

Packaging Features

Packaging Method	Piece
------------------	-------

Product Availability

Product Source	U.S.
----------------	------

Other

Brand	Raychem
-------	---------

Related Products

Not quite the product you're looking for?

[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)
- [Global Accessibility Statement](#)

Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed

