

Search by SKU, Product Name or Keyword

**SEARCH**

 **CART**

Product Information

**Contact Us**



MORE CHOICE



FREE SAMPLES



SHIPS TODAY



[Home](#)

[Fiber, Wire & Cable Manage...](#)

[Fiber Management](#)

[Fibre Reels & Guides](#)

[Fibre Reels](#)



**Fiber Reel - Fiber Storage, 30.0 mm Radius, 3.0 m of 900.0 mm Fiber Storage**

● In Stock 

Item Code: EFA04-10-001

Black Fiber Storage Reel routes fiber and stores up to 3.0 m of 900.0 mm Fiber of fiber. This UL94 V-0 Nylon 6/6 fiber reel is suitable for temperatures from .



Description	Quantity	Options
<b>Type</b> : Fiber Storage	<input type="text" value="100"/>	<div style="background-color: red; color: white; padding: 5px; text-align: center; margin-bottom: 5px;"><b>Add to Cart</b></div> <div style="background-color: #ccc; padding: 5px; text-align: center; margin-bottom: 5px;">Request CAD</div> <div style="background-color: #ccc; padding: 5px; text-align: center;">Request Quote</div>
<b>Radius</b> : 30.0 mm		
<b>Maximum Storage</b> : 3.0 m of 900.0 mm Fiber		
<b>Mounting Method</b> : Screw		
<b>Includes (All)</b> : No Mounting Hardware		
<b>Hole Diameter</b> : 2.8 mm (0.11 in)		
<b>Overall Height</b> : 3.9 mm (0.154 in)		
<b>Number of Mounting Holes</b> : 8		
<b>Color</b> : Black		
<b>Full Material</b> : Nylon 6/6		
<b>Material Flammability Standard</b> : UL94 V-0		
<b>Brand</b> : Richco		
<b>Material</b> : Nylon		
<b>Counterbore Hole Size</b> : 4.6 mm (0.181 in)		
<b>Package Quantity</b> : 100		

Downloads 



Print Page

**Recently Viewed**



Cable Clamp - Screw Mount, MS25281-R4, .250 in Bundle

Abrasives & Grinding  
 Access Hardware  
 Adhesives, Sealants & Tapes  
 Bearings & Power Transmissions  
 Caps & Plugs

Clamps & Workholdings  
 Cutting & Machining  
 Extrusions & Structural Systems  
 Fasteners  
 Feet, Casters & Glides

Fiber, Wire & Cable Management  
 Flange Protection  
 Knobs, Handles & Grips  
 Material Handling  
 Shop Supplies

PCB & Electronics Hardware  
 Pneumatics & Hydraulics  
 Raw Materials  
 Tamper Evident & Security Seals  
 Tooling & Positioning Components  
 Tools & Precision Instruments



**About Us**

About Essentra Components  
 About Essentra PLC  
 Locations  
 Knowledge Center

**Customer Service**

Contact Us  
 Catalogs  
 Sample Program  
 Free CAD  
 Careers  
 Distributor Portal

**Policies**

Privacy Policy  
 Terms and Conditions of Sale  
 Terms and Conditions of  
 Purchase  
 Environmental Policy  
 Health and Safety  
 Quality Statement

**Terms of Use**

Website Terms of Use  
 Cookie Policy

