

Search by SKU, Product Name or Keyword

**SEARCH**

**CART**



[Products](#) [Catalogs](#) [Free Samples](#) [Free CAD](#) [Knowledge Center](#) [Contact Us](#)

[Home](#) [Caps, Plugs & Masking](#) [Push Fit Caps](#) [Tube Caps & Bar Caps](#) [Round End Caps](#)



### Vinyl Round End Cap: .281 in (7.1 mm) ID, .500 in (12.7 mm) Inside Height, 350 °F (176.7 °C) Max. Temp.

● In Stock

**Item Code:** DM0281-1/2A

PVC Push Fit Vinyl Round End Cap has an I. D. of .281 in (7.1 mm) that can stretch onto larger dimensions for a snug fit. The Black glossy finish is attractive as a decorative end cap.



Description	Quantity	Options
<b>Inside Diameter</b> : .281 in (7.1 mm)	<input type="text" value="1"/>	<div style="background-color: red; color: white; padding: 5px; text-align: center; margin-bottom: 5px;"><b>Add to Cart</b></div> <div style="background-color: #ccc; padding: 5px; text-align: center; margin-bottom: 5px;">Request CAD</div> <div style="background-color: #ccc; padding: 5px; text-align: center; margin-bottom: 5px;">Free Sample</div> <div style="background-color: #ccc; padding: 5px; text-align: center;">Request Quote</div>
<b>Inside Height</b> : .500 in (12.7 mm)		
<b>Color</b> : Black		
<b>Material</b> : PVC		
<b>Fitting Style</b> : Push Fit		
<b>Full Material</b> : Polyvinyl Chloride		
<b>Temperature Range</b> : 350 °F (176.7 °C)		



Print Page

#### Recently Viewed



Vinyl Round End Cap: .281 in (7.1 mm) ID, .500 in (12.7 mm) Inside Height, 350 °F (176.7 °C) Max. Temp.

ESSENTIAL SOLUTIONS

DELIVERED

Abrasives & Grinding  
Access Hardware  
Adhesives, Sealants & Tapes  
Bearings & Power Transmissions  
Caps & Plugs

Clamps & Workholdings  
Cutting & Machining  
Extrusions & Structural Systems  
Fasteners  
Feet, Casters & Glides

Fiber, Wire & Cable Management  
Flange Protection  
Knobs, Handles & Grips  
Material Handling  
Shop Supplies

PCB & Electronics Hardware  
Pneumatics & Hydraulics  
Raw Materials  
Tamper Evident & Security Seals  
Tooling & Positioning Components  
Tools & Precision Instruments



[About Essentra Components](#)  
[About Essentra PLC](#)  
[Locations](#)  
[Knowledge Center](#)

[Contact Us](#)  
[Catalogs](#)  
[Sample Program](#)  
[Free CAD](#)  
[Careers](#)  
[Distributor Portal](#)

[Privacy Policy](#)  
[Terms and Conditions of Sale](#)  
[Terms and Conditions of Purchase](#)  
[Environmental Policy](#)  
[Health and Safety](#)  
[Quality Statement](#)

[Website Terms of Use](#)  
[Cookie Policy](#)

**ABOUT SSL CERTIFICATES**