

Data sheet

ISDN TE HUB 1/5 AP

Page 1/4

P/N
130345-01-E


EAN 4250184101772

2015-08-07

Illustrations



Dimensional drawing



See enlarged drawings at the end of document

Product specification

- surface-mounted and 1RU or 3RU rack-mounted
- ISDN TE HUB 1/5 is an active device and allows ISDN star-topology using the structured cabling of the building
- one equipped 8-wire RJ45 input jack
- 5 equipped 8-wire output jacks for max. cable lengths of 150 m
- cascable
- terminating resistors can be deactivated
- terminating resistors are required on wall outlets
- all outputs fully bus-capable (reduced max. cable length)
- connection to ISDN line or after phone system
- two indicators for operational availability and bus activities
- mounting in different distributor types (10 inch, 19 inch, top hat rail distributor, etc.) by means of suitable supports or surface mounting
- low power consumption; therefore, high feeding capacity available for terminals
- for max. 3 non-fed ISDN terminals (also with power supply unit)
- no external power supply required; power is supplied from the ISDN-S0 connection (if NTBA supplies power)
- variants: surface-mounted unit, rack-mounted module

Data sheet
ISDN TE HUB 1/5 AP

Page 2/4

P/N
130345-01-E
EAN 4250184101772

2015-08-07

Technical Data

General Data

Fields of application	Structured building cabling, Data center
Design	ISDN
Color	light gray
Dimensions	
Dimension (L x W x H)	118.00 x 121.50 x 37.70 mm
Dimension (L x W x H)	4.65 x 4.78 x 1.48 in.

Connections/interfaces

Connector technology interface 2	RJ45-jack
Number of ports interface 2	5
Number of ports interface 2 equipped	5

Mechanical characteristics

Position/mounting of latch - standard installation position	top and bottom
---	----------------

Environmental conditions

Temperature (min. - max.)	
Temperature - Storage °C	-40 - 70 °C
Temperature - Storage °F	-40 - 158 °F
Temperature - Operating °C	-40 - 70 °C
Temperature - Operating °F	-40 - 158 °F

Certifications

Gost Certification	yes
--------------------	-----

Approvals

RoHS	compliant
------	-----------

Classifications

ETIM 5.0	EC001677
----------	----------

© 2015 METZ CONNECT - Technische Änderungen vorbehalten! Subject to modifications! Sous réserve de modifications techniques!



Data sheet
ISDN TE HUB 1/5 AP

Page 3/4

P/N
130345-01-E
EAN 4250184101772

2015-08-07

Technical Data**Packing details**

Type of packaging	1 pc(s) / box
Packaging unit - Weight (gram)	701.00 g
Packaging unit - Weight (pound)	1.55 lb
Packaging dimension (W x H x D)	145.00 x 134.00 x 70.00 mm
Packaging dimension (W x H x D)	5.71 x 5.28 x 2.76 in.

**Data sheet
ISDN TE HUB 1/5 AP**

Page 4/4

**P/N
130345-01-E
EAN 4250184101772**

2015-08-07

Illustrations

Dimensional drawing

