

Product data sheet

Specifications



graphic display terminal, Altivar, 240 x 160pixels, IP65

VW3A1111

Product availability: Stock - Normally stocked in distribution facility

Main

Range of Product	Altivar
Range Compatibility	Altivar Process ATV900 Altivar Process ATV600 Altivar Machine ATV340
Accessory / separate part category	Display and signalling accessories
Accessory / Separate Part Type	Display terminal
Accessory / separate part destination	Variable speed drive
Product Specific Application	To control, adjust and configure the drive To save and download configurations To display the current values
IP Degree of Protection	IP65

Complementary

User Language	Spanish Romanian Turkish Polish Swedish Estonian Bulgarian English Russian Greek Danish Hungarian Chinese Norwegian Lithuanian French Brazilian German Korean Portuguese Finnish Czech Slovak Taiwanese Dutch Italian Ukrainian
Realtime clock	Built-in
Battery Size	CR2032
Battery life	10 year(s)
Display type	Backlit LCD screen white and red
Messages display capacity	8 lines
Pixel resolution	240 x 160

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Net Weight	0.4 lb(US) (0.2 kg)
------------	---------------------

Environment

Ambient Air Temperature for Operation	5...140 °F (-15...60 °C)
---------------------------------------	--------------------------

Ordering and shipping details

Category	US1CP4E22205
----------	--------------

Discount Schedule	CP4E
-------------------	------

GTIN	3606480702235
------	---------------

Returnability	Yes
---------------	-----

Country of origin	ID
-------------------	----

Packing Units

Unit Type of Package 1	PCE
------------------------	-----

Number of Units in Package 1	1
------------------------------	---

Package 1 Height	2.28 in (5.800 cm)
------------------	--------------------

Package 1 Width	5.51 in (14.000 cm)
-----------------	---------------------

Package 1 Length	7.40 in (18.800 cm)
------------------	---------------------

Package 1 Weight	10.018 oz (284.000 g)
------------------	-----------------------

Unit Type of Package 2	S03
------------------------	-----

Number of Units in Package 2	20
------------------------------	----

Package 2 Height	11.81 in (30.000 cm)
------------------	----------------------

Package 2 Width	11.81 in (30.000 cm)
-----------------	----------------------

Package 2 Length	15.75 in (40.000 cm)
------------------	----------------------

Package 2 Weight	14.330 lb(US) (6.500 kg)
------------------	--------------------------

Unit Type of Package 3	P06
------------------------	-----

Number of Units in Package 3	80
------------------------------	----

Package 3 Height	17.72 in (45.000 cm)
------------------	----------------------

Package 3 Width	23.62 in (60.000 cm)
-----------------	----------------------

Package 3 Length	31.50 in (80.000 cm)
------------------	----------------------

Package 3 Weight	72.259 lb(US) (32.776 kg)
------------------	---------------------------

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Carbon footprint (kg CO2 eq, Total Life cycle) 104

Environmental Disclosure [Product Environmental Profile](#)

Use Better

Materials and Substances

Packaging made with recycled cardboard No

Packaging without single use plastic Yes

[EU RoHS Directive](#) Pro-active compliance (Product out of EU RoHS legal scope)

SCIP Number Cd0eb1b0-0b52-4d45-90f6-4bd8d825785f

REACH Regulation [REACH Declaration](#)

California proposition 65 **WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov**

PVC free Yes

Use Again

Repack and remanufacture

Circularity Profile [End of Life Information](#)

Take-back No

Image of product / Alternate images

Alternative





