



**SCHROFF**

Project - 0 item(s)

**MY PROJECT LIST**

- PRODUCTS**
- APPLICATIONS**
- INDUSTRIES**
- NEW PRODUCTS**
- CONFIGURATORS**
- Products ▾
- Search
- 🔍

Home > Guide rail, 160 mm deep



## Guide rail, 160 mm deep

**SCHROFF**



**Catalog Number: 64560-096**

[Back To Product](#)

- Can be clipped into 1.5 mm thick plate
- Plastic guide rail, one piece, red
- Storage temperature: from -40 °C ... 130 °C
- Assembly
- Can be clipped into horizontal rails in Al extrusion
- For 2.5 mm groove width

**Product family:**

EuropacPRO

**Type:**

Individual Components

**Individual Component Type:**


Guide Rails & Accessories

**Standard pack quantity (SPQ):**

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.



Other Views



**Select product specifications before modifying or adding to project list or requesting a quote.**

Depth-mm-defining

160

[Clear Selection](#)

Quantity

**Add Item to Project List +**


**Links**

Native CAD files

### Technical Data

<b>Length mm</b>	160.0
<b>Qty</b>	1 piece (SPQ 50)
<b>Delivery is exclusively made in Standard Pack Quantity (SPQ)</b>	50
<b>Color</b>	red
<b>Groove width</b>	2.5
<b>Material</b>	PBT, UL 94 V-0
<b>Description</b>	For plug-in units and frame type plug-in units

### Accessories



Panhead screw, Torx (2.5x9.3), self-tapping,  
steel zinc plated, PU 100 pcs

24560-  
141

[Add Item to Project List +](#)

#### EXPLORE

- [About Us](#)
- [Services & Capabilities](#)
- [News & Events](#)
- [Newsletter Subscriptions](#)
- [Strategic Partnerships](#)
- [Investor Relations](#)

#### CONTACT

- [Customer Service](#)
- [Find a Sales Office or Distributor](#)
- [Global Locations](#)
- [Product Compliance & Certifications](#)
- [Partner Login](#)

#### DOWNLOAD

- [Download Center](#)
- [Reference Projects](#)
- [Videos](#)
- [Product Configurators](#)
- [Warranties and Terms of Sale & Procurement](#)

© 2018 nVent. All rights reserved | [Privacy Policy](#) | [Terms of Use](#) | [Cookie Policy](#) | [Imprint](#) | [Site Map](#)

#### Connect With Us

