




Wire Protection & Management > Wiring Ducts & Accessories > Wiring Ducts & Covers >

Wiring Duct: PC-ABS Material, Gray, 2 meters, Flame-Retardant



Wiring Duct Product Type: **Wiring Duct**

Primary Product Material: **PC-ABS**

Product Height: **40 mm [1.575 in]**

Product Length: **2000 mm [78.74 in]**

Product Width: **60 mm [2.362 in]**

[All Wiring Duct: PC-ABS Material, Gray, 2 meters, Flame-Retardant \(11\)](#)

Features

Product Type Features

Wiring Duct Product Type	Wiring Duct
--------------------------	-------------

Body Features

Primary Product Color	Gray
Primary Product Material	PC-ABS

Dimensions

Product Height	40 mm[1.575 in]
Product Length	2000 mm[78.74 in]
Product Width	60 mm[2.362 in]

Usage Conditions

Operating Temperature Range	-25 – 90 °C[-13 – 194 °F]
-----------------------------	---------------------------

Packaging Features

Packaging Quantity	18
--------------------	----



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1SET411404R0000
WD-1-TL-0004



TE Part # 1SET411407R0000
WD-1-TL-0007



TE Part # 1SET411402R0000
WD-1-TL-0002



TE Part # 1SET411401R0000
WD-1-TL-0001

1SET411107R0000

Wiring Duct, PC-ABS, 40 mm [1.575 in] Height, 2000 mm [78.74 in] Length, 60 mm [2.362 in] Width, -25 – 90 °C [-13 – 194 °F]



TE Part # 1SET411252R0000
[WD-1-CH-GR060](#)

Customers Also Bought



TE Part #1SNK508010R0000
[ZS10](#)



TE Part #1SNK505010R0000
[ZS4](#)




TE Part #1SNK516010R0000
[ZS35](#)



TE Part #1SNK522010R0000
[ZS70](#)



TE Part #1SET411104R0000
[WD-1-DH-GR4040](#)



TE Part #9-160463-2
[FASTON, PGYBCK, PIDG, BRASS, .250, 16-14](#)



TE Part #350547-2
[UMNL PIN 20-14 AUBR L/P](#)



TE Part #794282-1
[15P UMNL WIRE SEAL](#)



TE Part #926307-1
[6P UNIV.M-N-L.CAP](#)



TE Part #4-1393779-4
[V23101D1106B201\(stronger packaging\)](#)

Documents

Product Drawings

[WD-1-DH-GR6040](#)

French

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_1SET411107R0000_A.2d_dxf.zip](#)

1SET411107R0000

Wiring Duct, PC-ABS, 40 mm [1.575 in] Height, 2000 mm [78.74 in] Length, 60 mm [2.362 in] Width, -25 – 90 °C [-13 – 194 °F]



English

Customer View Model

[ENG_CVM_CVM_1SET411107R0000_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1SET411107R0000_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Infographic - entrelec ews-linecard](#)

English

[Datasheet - ENTRELEC-wiring-duct-DS](#)

English

[Datasheet - Entrelec Electrical-Solutions](#)

[Essential Entrelec Terminal Blocks](#)

French

[Essential Entrelec Terminal Blocks](#)

English

[Essential Entrelec Terminal Blocks](#)

Japanese

Agency Approvals

[Agency Approval Document](#)

English

[Agency Approval Document](#)

English