

1SET411203R0000 ✓ ACTIVE

ENTRELEC

TE Internal #: 1SET411203R0000

Wiring Duct Cover, PVC, 9.1 mm [.358 in] Height, 2000 mm [78.74 in] Length, 60 mm [2.362 in] Width, -5 – 60 °C [23 – 140 °F]

[View on TE.com >](#)



Wire Protection & Management > Wiring Ducts & Accessories > Wiring Ducts & Covers > Wiring Duct Covers: PVC, Gray, 2 meters [2000mm]



Wiring Duct Product Type: **Wiring Duct Cover**

Primary Product Material: **PVC**

Product Height: **9.1 mm [.358 in]**

Product Length: **2000 mm [78.74 in]**

Product Width: **60 mm [2.362 in]**

[All Wiring Duct Covers: PVC, Gray, 2 meters \[2000mm\] \(6\)](#)

## Features

### Product Type Features

|                          |                   |
|--------------------------|-------------------|
| Wiring Duct Product Type | Wiring Duct Cover |
|--------------------------|-------------------|

### Body Features

|                          |      |
|--------------------------|------|
| Primary Product Color    | Gray |
| Primary Product Material | PVC  |

### Dimensions

|                |                   |
|----------------|-------------------|
| Product Height | 9.1 mm[.358 in]   |
| Product Length | 2000 mm[78.74 in] |
| Product Width  | 60 mm[2.362 in]   |

### Usage Conditions

|                             |                         |
|-----------------------------|-------------------------|
| Operating Temperature Range | -5 – 60 °C[23 – 140 °F] |
|-----------------------------|-------------------------|

### Packaging Features

|                    |   |
|--------------------|---|
| Packaging Quantity | 3 |
|--------------------|---|

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

|   |   |
|---|---|
| EU RoHS Directive 2011/65/EU                  | Compliant   |
| EU ELV Directive 2000/53/EC                   | Out of Scope  |
| China RoHS 2 Directive MIIT Order No 32, 2016 | 有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold   |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JUNE 2025 (250)<br>Candidate List Declared Against: JUNE 2023 (235)<br>Does not contain REACH SVHC |
| Halogen Content                               | Not Low Halogen - contains Br or Cl > 900 ppm.  |
| Solder Process Capability                     | Not reviewed for solder process capability  |

### Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



TE Part # CAT-Z62-W1-DP  
PVC Wiring Duct: 2 meters, Gray  
Color, Flame-Retardant

## Customers Also Bought



## Documents

### Product Drawings

[WD-1-CP-GR060](#)

French

### CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_1SET411203R0000\\_A.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_1SET411203R0000\\_A.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_1SET411203R0000\\_A.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Datasheets & Catalog Pages

[Infographic - entrelec ews-linecard](#)

English

[Datasheet - ENTRELEC-wiring-duct-DS](#)

English

[Datasheet - Entrelec Electrical-Solutions](#)

[Essential Entrelec Terminal Blocks](#)

French

[Essential Entrelec Terminal Blocks](#)

1SET411203R0000

Wiring Duct Cover, PVC, 9.1 mm [.358 in] Height, 2000 mm [78.74 in] Length, 60 mm [2.362 in] Width, -5 – 60 °C [23 – 140 °F]



English

[Essential Entrelec Terminal Blocks](#)

Japanese

---

[Agency Approvals](#)

[Agency Approval Document](#)

English