

## General Information

Extended Product Type:	MB4/6.P5
Product ID:	1SNA165423R1500
EAN:	3472591654233
Catalog Description:	MB4/6.P5 Distribution Terminal Blocks
Long Description:	MB4/6.P5 Distribution Terminal Blocks - Yellow,4mm&#178; RatedCrossSection, 32.5mm Spacing G32, TH 35-7.5, TH 35-15 Rail.

## Categories

Products » Low Voltage Products and Systems » Connection Devices » Terminal Blocks » Solution Series

## Ordering

Color:	green/yellow
Minimum Order Quantity:	5 piece
Customs Tariff Number:	85369010

## Popular Downloads

Data Sheet, Technical Information:	1SNC160001C0207-CH-G Distribution terminals
Instructions and Manuals:	1SNC160001C0207-CH-G Distribution terminals

## Dimensions

Product Net Width:	32.5 mm
Product Net Height:	44.5 mm
Product Net Depth:	40.5 mm
Product Net Weight:	50 g

## Technical

Rated Cross-Section:	4 mm&#178;
Spacing:	6 mm
Connection Type:	Screw clamp
Function:	Distribution
Number of Levels:	1
Rated Impulse Withstand Voltage (U <sub>imp</sub> ):	8 kV
Pollution Degree:	2
Mounting on DIN Rail:	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Wire Stripping Length:	9.5 mm
Recommended Screw Driver:	4 mm
Tightening Torque:	acc. IEC 60947-1 0.5 N&#183;m Manufacturer 0.8 N&#183;m

## Technical UL/CSA

Flammability According to UL94:	V2
---------------------------------	----

## Environmental

RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment
--------------	---

## Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	1SND225007U1000
EAC Certificate:	1SND161009A1100
RoHS Information:	1SND230023F0202

## Classifications

Object Classification Code:	X
ETIM 4:	EC001894 - Distributor assembly terminal blocks
ETIM 5:	EC001894 - Distributor assembly terminal blocks
ETIM 6:	EC001894 - Distributor assembly terminal blocks

## Container Information

Package Level 1 Units:	5 piece
------------------------	---------

<b>Package Level 1 Width:</b>	61 mm
<b>Package Level 1 Length:</b>	176 mm
<b>Package Level 1 Height:</b>	47 mm
<b>Package Level 1 Gross Weight:</b>	0.25 kg
<b>Package Level 1 EAN:</b>	3472591654233
<b>Package Level 2 Units:</b>	120 piece
<b>Package Level 3 Units:</b>	5760 piece
<b>Product Packing Type:</b>	Box

