

## General Information

Extended Product Type:	M150/35.EE
Product ID:	1SNA115156R1700
EAN:	3472591151565
Catalog Description:	M150/35.EE Stud Terminal Blocks
Long Description:	M150/35.EE Power Terminal Blocks Feed-through.

## Categories

Products » Low Voltage Products and Systems » Connection Devices » Terminal Blocks » Solution Series

## Ordering

Color:	grey
Minimum Order Quantity:	10 piece
Customs Tariff Number:	85369010

## Popular Downloads

Data Sheet, Technical Information:	1SNC160001C0207-CH-D Power terminals
Instructions and Manuals:	1SNC160001C0207-CH-D Power terminals

## Dimensions

Product Net Width:	35 mm
Product Net Height:	94 mm
Product Net Depth:	52 mm
Product Net Weight:	190 g

## Technical

Rated Cross-Section:	95 mm <sup>2</sup>
Spacing:	35 mm
Connection Type:	Stud
Function:	Feed-through
Number of Levels:	1
Rated Impulse Withstand Voltage (U <sub>imp</sub> ):	12 kV
Dielectric Test Voltage:	3500 V
Pollution Degree:	2
Insulation Material:	Polyamide
Mounting on DIN Rail:	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Tightening Torque:	Cable Lug 10 N·m Central Bolt 6 N·m

## Technical UL/CSA

Flammability According to UL94:	V2
---------------------------------	----

## Environmental

Ambient Air Temperature:	Operation -55 ... +110 °C Storage -55 ... +110 °C
RoHS Status:	Following EU Directive 2011/65/EC

## Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	1SND225011U1000
EAC Certificate:	1SND161009A1100
RoHS Information:	1SND230022F0204

## Classifications

Object Classification Code:	X
ETIM 4:	EC000897 - Feed-through terminal block
ETIM 5:	EC000897 - Feed-through terminal block
ETIM 6:	EC000897 - Feed-through terminal block

## Container Information

<b>Package Level 1 Units:</b>	10 piece
<b>Package Level 1 Width:</b>	176 mm
<b>Package Level 1 Length:</b>	200 mm
<b>Package Level 1 Height:</b>	75 mm
<b>Package Level 1 Gross Weight:</b>	1.9 kg
<b>Package Level 1 EAN:</b>	3472591151565
<b>Package Level 2 Units:</b>	90 piece
<b>Package Level 3 Units:</b>	2160 piece
<b>Product Packing Type:</b>	Box

---

