

# Weatherproof metallic boxes

## Universal boxes and covers

### Single-gang

	Cat. No.	Hub size (in.)	Color	Std. ctn.
<b>Three outlets</b>				
	IH3-1	1/2	Silver	50
	IH3-2	3/4	Silver	50
	IH3-1-LM•	1/2	Silver	50
	IH3-2-LM•	3/4	Silver	50
	D-PAK			
	DIH3-1-LM•	1/2	Silver	10
	DIH3-1-LM-BR•	1/2	Bronze	10
	DIH3-1-LM-WH•	1/2	White	10
	DIH3-2-LM•	3/4	Silver	10
	B13030G	1	Silver	10
<b>Four outlets</b>				
	IH4-1	1/2	Silver	50
	IH4-2	3/4	Silver	50
	IH4-1-LM•	1/2	Silver	50
	IH4-2-LM•	3/4	Silver	50
	D-PAK			
	DIH4-1-LM•	1/2	Silver	10
	DIH4-1-LM-BR•	1/2	Bronze	10
	DIH4-1-LM-WH•	1/2	White	10
DIH4-2-LM•	3/4	Silver	10	
<b>Five outlets</b>				
	IH5-1	1/2	Silver	25
	IH5-2	3/4	Silver	25
	IH5-1-LM•	1/2	Silver	25
	IH5-2-LM•	3/4	Silver	25
	D-PAK			
	DIH5-1-LM•	1/2	Silver	10
DIH5-2-LM•	3/4	Silver	10	
<b>Five outlets (2-side)</b>				
	B1501SGR	1/2	Silver	16
	B1502SG	3/4	Silver	25
<b>Six outlets (3-side)</b>				
	IH6S2-1•	1/2	Silver	25
	IH6S2-2•	3/4	Silver	25

Note: Raintight when used with appropriate Red•Dot® covers. Boxes supplied with 2 closure plugs and ground screw.  
 • With mounting lugs

### Two-gang

	Cat. No.	Hub Size (in.)	Color	Std. ctn.
<b>Three outlets</b>				
	2IH3-1•	1/2	Silver	10
	2IH3-2•	3/4	Silver	10
	D-PAK			
2IH3-1	D2IH3-1	1/2	Silver	6
<b>Four outlets</b>				
	2IH4-1•	1/2	Silver	10
	2IH4-2•	3/4	Silver	10
<b>Five outlets</b>				
	2IH5-1•	1/2	Silver	10
	2IH5-2•	3/4	Silver	10
2IH5-1	<b>Five outlets (2-side)</b>			
	2IH5S2-1•	1/2	Silver	10
	2IH5S2-2•	3/4	Silver	10
	B25D30G	1	Silver	10
2IH5S2-1	<b>Seven outlets</b>			
	2IH7-1•	1/2	Silver	10
	2IH7-2•	3/4	Silver	10
2IH7-1	<b>Seven outlets (2-side)</b>			
	2IH7S2-1•	1/2	Silver	10
	2IH7S2-2•	3/4	Silver	10
2IH7S2-1				

Note: Raintight when used with appropriate Red•Dot® covers. Boxes supplied with 2 closure plugs and ground screw.  
 • With mounting lugs