



Family

Catalog Number: NVNZ-M202S/P3
Product ID: 7TAA292150R0710
UPC Number: 78620996443
EAN Number: 07630030255090
Status: A

VNZ Connector Straight, Metric Metal Thread with Strain Relief IP68 - Thread M20x1.5, Conduit Size NW 12, Clamping Range 6.5-9.5, with Sealing Insert, Color Black

North American Specifications (UNSPSC)

| | |
|-------------|--|
| UNSPSC | 39121719 Strain reliefs |
| IGCC | 5067 Strain reliefs |
| Type | Fittings for Nylon Flexible Conduits |
| Application | Use In Railway Vehicle and Heavy Machine Construction and for the Separation of Damp and Dry Areas |
| Size | NW12 ; M20x1.5 |
| Material | Polyamide 6 with Nickel Plated Brass Threads |
| Color | Black |

European Specifications (ETIM)

| | |
|--|---|
| ETIM | EC001176 Screw connection for corrugated plastic hose |
| Nominal diameter | 16mm |
| Degree of protection (IP) | IP68 |
| Model | Straight |
| Revolving thread | N |
| Construction type | Internal thread |
| Type of connection | Snap connection |
| Thread type | Metric |
| Thread connection size | M20 x 1.5 |
| Thread material | Brass |
| Thread length | 6mm |
| Total length | 54mm |
| Material | Polyamide |
| Material sealing | TPE |
| Colour | Black |
| Approved in combination with protective conduit CSA | N |
| Approved in combination with protective conduit UR | Y |
| Approved in combination with protective conduit DIN EN 61386-23 | N |
| Approved in combination with protective conduit Lloyd's Register | N |
| Operating temperature | -40 - +105°C |

Packaging

| | |
|---------------------------|---------------------|
| Inner Quantity | 50 |
| Outer Quantity | 300 |
| Outer Dimensions (inches) | 15.748x11.811x7.874 |
| Weight Uom | 0.08 lbs. Each |

Documents / Support Tools

| | |
|--------------|----------------------|
| Catalog Page | Available on Website |
|--------------|----------------------|

Header

| | |
|----------|----------------------|
| 3D Model | Available on Website |
|----------|----------------------|

For further technical assistance, please contact us...

ABB Installation Products - USA
860 Ridge Lake Blvd.
Memphis, TN 38120
www.tnb.com

ABB Installation Products Technical Support
MS 3B-50
860 Ridge Lake Blvd.
Memphis, TN 38120

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com