




SL Series 110Connect Category 6 Modular Jacks




Wiring Pattern		Part Number
T568A/T568B	Unshielded	1375055-X
		With Dust Cover 1375187-X
	Shielded	180° (Rear) Entry 1375188-1*
		90° (Side) Entry 1479552-1*

X denotes color: -1 = Almond, -2 = Black, -3 = White, -4 = Gray, -5 = Orange, -6 = Blue, -7 = Red, -8 = Yellow, -9 = Green, 1--0 = Violet, 1--1 = Electrical Ivory

*Note: Shielded jacks are not available in colors and do not accept strain reliefs.
NOTE: Highlighted part numbers are routinely stocked for shortest lead times.

SL Series 110Connect Category 5E Modular Jacks




Wiring Pattern		Part Number
T568A/T568B	Unshielded	1375191-X
		With Dust Cover 1375190-X
	Shielded	180° (Rear) Entry 1375189-1*
		90° (Side) Entry 1479717-1*

X denotes color: -1 = Almond, -2 = Black, -3 = White, -4 = Gray, -5 = Orange, -6 = Blue, -7 = Red, -8 = Yellow, -9 = Green, 1--0 = Violet, 1--1 = Electrical Ivory

*Note: Shielded jacks are not available in colors and do not accept strain reliefs.
NOTE: Highlighted part numbers are routinely stocked for shortest lead times.

SL Series 110Connect Category 3 Modular Jacks



Wiring Pattern		Part Number
RJ11c/RJ14c/RJ25c	Unshielded	1375192-X
		With Dust Cover 1375193-X

X denotes color: -1 = Almond, -2 = Black, -3 = White, -4 = Gray, -5 = Orange, -6 = Blue, -7 = Red, -8 = Yellow, -9 = Green, 1--0 = Violet, 1--1 = Electrical Ivory

NOTE: Highlighted part numbers are routinely stocked for shortest lead times.

Product Facts

- :: Thin profile improves outlet density
- :: Modular Jacks available with integral dust covers
- :: 180° or 90° cable dress for easy termination
- :: Universal wiring label permits wiring to T568A or T568B
- :: Meet or exceed all TIA and ISO component performance requirements
- :: Compatible with faceplates found in this catalog
- :: Bend-limiting strain relief included with unshielded jacks
- :: UL Listed: E81956
- :: 8-Position RJ45 Modular Jacks for 1-, 2-, 3- and 4-Pair applications
- :: Can be terminated with either SL Series Modular Jack Termination Tool (1725150-1 on page 151) or standard 110 punch-down tools (on page 152)

Product Facts

- :: Thin profile improves outlet density
- :: Modular Jacks available with integral dust covers
- :: 180° or 90° cable dress for easy termination
- :: Compatible with faceplates found in this catalog
- :: UL Listed: E81956
- :: 6-Position RJ11c/RJ14c/RJ25c Modular Jacks for 1-, 2- and 3-Pair applications
- :: Can be terminated with either SL Series Modular Jack Termination Tool (1725150-1 on page 151) or standard 110 punch-down tools (on page 152)