

Specification Sheet

Part Number: 126-00000

Edge Clip applies easily to plastic and metal sheets without the need for a mounting hole.



Edge Clip provides low insertion force and high extraction force ideal for assembly environments.

Cable tie is outside serrated to reduce bundle chafing.

1-Piece Cable Tie with Edge Clip, 8" Long, EC13, Panel Thickness 0.04 - 0.12", 50 lbs, PA66HS, Black, 500/bg

Article Number 126-00000

Type T50SOSEC13E

Color Black (BK)

Quantity Per pack

Product Description The cable tie and edge clip assembly is ideal for use where holes are not acceptable or where adhesives will fail due to temperature problems. Edge clips are widely used for fixing and bundling cables and wires within automotive, trucking, heavy equipment, solar panel, wind power, and white goods equipment manufacturing.

Short Description 1-Piece Cable Tie with Edge Clip, 8" Long, EC13, Panel Thickness 0.04 - 0.12", 50 lbs, PA66HS, Black, 500/bg

Global Part Name T50SOSEC13E-PA66HS-BK

Minimum Tensile Strength (Imperial) 40

Minimum Tensile Strength (Metric) 180

Length L (Imperial) 6.0

Length L (Metric) 160.0

Fixation Method Edge Clip

Identification Plate Position none

Releasable Closure No

Tie Closure plastic pawl

Variant Outside Serrated

Width W (Imperial) 0.18

Width W (Metric) 4.6

Bundle Diameter Min (Imperial) 0.04

Bundle Diameter Min (Metric) 1.0

Bundle Diameter Max (Imperial) 1.38

Bundle Diameter Max (Metric) 35.0

Thickness T (Imperial) 0.05

Thickness T (Metric) 1.35

Height H (Imperial) 0.06

Height H (Metric) 1.35

Panel Thickness Min (Imperial) 0.04

Panel Thickness Max (Imperial) 0.12

Panel Thickness Min (Metric) 1.0

Panel Thickness Max (Metric) 3.0

Material Polyamide 6.6 heat stabilized (PA66HS)

Material Shortcut PA66HS

Flammability UL 94 V-2

UV Resistant (Yes/No) No

Use Conditions For Indoor and Outdoor Use

Operating Temperature -40°F to +221°F (-40°C to +105°C)

Reach Compliant (Article 33) Yes

ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)