


Specification Sheet

Part Number: 181-93008



A temporary film is applied to the covers to protect against scratches and is writable for identification during installation.

Cover is flush with the side of the duct for increased wire capacity and allows for tight, side by side duct placement.

Covers are provided with a non-slip lining, which insures the covers remain in place during vibration, yet they easily snap on and off. (Covers to be purchased separately)

Wiring Duct Cover for 3" Duct, 6 ft Long, PVC, Gray, 120 ft/carton

|                     |                                                                                                                                                                                                                                                                                                                     |
|---------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Article Number      | 181-93008                                                                                                                                                                                                                                                                                                           |
| Type                | TC3                                                                                                                                                                                                                                                                                                                 |
| Color               | Gray (GY)                                                                                                                                                                                                                                                                                                           |
| Quantity Per        | carton                                                                                                                                                                                                                                                                                                              |
| Product Description | HellermannTyton’s Pro-Duct wiring duct covers are sold separately and interchangeable among the 3 styles of duct (solid, slotted and high density). Manufactured from high impact, rigid PVC, Pro-Duct covers come in standard colors of white, gray and black. Wiring duct covers are available in 6 foot lengths. |
| Short Description   | Wiring Duct Cover for 3" Duct, 6 ft Long, PVC, Gray, 120 ft/carton                                                                                                                                                                                                                                                  |

|                              |                         |
|------------------------------|-------------------------|
| Global Part Name             | TC3-PVC-GY              |
| Length L (Imperial)          | 6.0                     |
| Length L (Metric)            | 1.83                    |
| Width W (Imperial)           | 3.0                     |
| Width W (Metric)             | 76.2                    |
| Height H (Imperial)          | 0.308                   |
| Height H (Metric)            | 7.82                    |
| Material                     | Polyvinylchloride (PVC) |
| Material Shortcut            | PVC                     |
| Flammability                 | UL 94 V-0               |
| Halogen Free                 | No                      |
| UV Resistant (Yes/No)        | No                      |
| Use Conditions               | For Indoor Use Only     |
| Operating Temperature        | +122°F (+50°C)          |
| Reach Compliant (Article 33) | No                      |

|                             |                                                  |
|-----------------------------|--------------------------------------------------|
| ROHS Compliant              | Yes                                              |
| Certification/Specification | EN 50085-1:2005 + A1:2013 CSA EN 50085-2-3_1A UL |
| UL Recognized (US)          | Yes                                              |
| Package Quantity (Imperial) | 120.0                                            |
| Package Quantity (Metric)   | 36.58                                            |
| Customs Number              | 3925900000                                       |

7930 N. Faulkner Road, Milwaukee, WI 53224  
 Phone: (800) 537-1512 | Email: corp@htamericas.com