


Data Sheet | Item Number: 206-2115

VDE slot screwdriver; 5.5 x 1.0 x 125; VDE tested; 1000 V; insulated; 2-component grip; size 2 (110 mm); green/gray

<https://www.wago.com/206-2115>



Color: ☐ green/gray



Notes

Safety Information

- Always use the appropriate VDE screwdriver variant for your screw head variant to prevent injury from slipping and damage to the VDE screwdriver or screw head.
- Keep the VDE screwdriver free from oil, grease and moisture to prevent slipping and potential injury.
- If the tip is damaged, replace the VDE screwdriver to prevent slipping and injury.
- Do not use the VDE screwdriver if the handle or insulation is damaged to prevent the risk of electric shock.
- Do not use the VDE screwdriver to open the contact spring on products with operating slots.
- Do not use the VDE screwdriver as a prying tool or chisel.
- Wear approved eye protection and the necessary personal protective equipment for your application.
- Environmental and storage information: Ensure that VDE screwdrivers are not exposed to strong heat sources (e.g., heating pipes or steam lines) or to UV radiation.

Safety information 2

1. Work on live or load-carrying parts may only be performed by properly trained and qualified personnel.
2. Use only for its intended purpose!
3. Observe national regulations, standards and guidelines!
4. Follow the technical specifications of the products!
5. Do not use soiled components!
6. Use only compatible bits and drives!



Physical data		
Width		27 mm / 1.063 inches
Height		25 mm / 0.984 inches
Depth		235 mm / 9.252 inches
Blade length		125 mm
Grip length		110 mm

Mechanical data		
Tip type	Tip type	5.5 x 1.0
Continuous blade		No
Blade type		Straight
Roll-away protection		Yes
Hanging eyelet		Yes
Grip marking		Yes
Head marking		Yes

Material data		
Color		green/gray
Material 1		Polypropylen (PP)
Material 2		Thermoplastische Elastomere (TPE)
Fire load		0 MJ
Blade material		61CrSiV5
Blade surface		Burnished
Weight		73 g

Commercial data		
PU (SPU)		1 pcs
Packaging type		unpacked
Country of origin		DE
GTIN		4066966459005
Customs tariff number		8205400000

Product Classification		
UNSPSC		27111701
ETIM 9.0		EC000158
ETIM 8.0		EC000158
ECCN		NO US CLASSIFICATION

Environmental Product Compliance		
RoHS Compliance Status		Compliant,No Exemption



Downloads	
Environmental Product Compliance	
Compliance Search	
Environmental Product Compliance 206-2115	