


Data Sheet | Item Number: 711-402

Transformer fuse terminal block; for fuse 6.35 x 32 mm; CAGE CLAMP® connection for conductors; 22.5 mm wide; gray

<https://www.wago.com/711-402>

DISCONTINUED:

31.12.2024



Color: ■ gray

Transformatorklemmen Serie 711 mit CAGE CLAMP®

Bei diesen Transformator-klemmen mit der Artikelnummer 711-402 steht eine schnelle und sichere Verbindung im Fokus. Diese Transformator-klemmen benötigen für den Leiteranschluss eine Abisolierlänge zwischen 9 und 10 mm. Dieses Produkt ist mit der CAGE CLAMP®-Technologie ausgestattet. Der zuverlässige und wartungsfreie CAGE CLAMP® Universalanschluss ermöglicht den Anschluss aller Leiterarten mit einer Käfigzugfeder. Eine Vorbehandlung der Leiter, z.B. durch das Aufcrimpen von Aderendhülsen, ist nicht erforderlich. In Breite x Höhe x Tiefe sind die Abmessungen (22,5 x 57,1 x 23,5) mm.

Electrical data

Ratings per	IEC/EN 60664-1		
Overvoltage category	III	III	II
Pollution degree	3	2	2
Nominal voltage	-	800 V	-
Rated surge voltage	-	8 kV	-
Rated current	-	10 A	-

Connection data

Clamping units	1
Total number of potentials	1
Number of connection types	1

Connection 1

Connection technology	CAGE CLAMP®
Strip length	9 ... 10 mm / 0.35 ... 0.39 inches

Physical data

Width	22.5 mm / 0.886 inches
Height	57.1 mm / 2.248 inches
Depth	23.5 mm / 0.925 inches

Material data

Note (material data)	Information on material specifications can be found here
Color	gray
Material group	I
Insulation material (main housing)	Polyamide (PA66)
Flammability class per UL94	V0
Fire load	0.242 MJ
Weight	13.4 g

Commercial data

PU (SPU)	100 pcs
Packaging type	Box
Country of origin	DE
GTIN	4044918684569
Customs tariff number	85369095000
End of Sale	2024-12-31
End of Production	2025-10-01
End of Delivery	2025-11-28
End of Service and Repair	2026-12-01

Product Classification

UNSPSC	39121410
eCl@ss 10.0	27-14-11-10
eCl@ss 9.0	27-14-11-10
ETIM 9.0	EC000398
ETIM 8.0	EC000398
ECCN	NO US CLASSIFICATION

Environmental Product Compliance

RoHS Compliance Status	Compliant, No Exemption
------------------------	-------------------------

Approvals / Certificates

General approvals



Approval	Standard	Certificate Name
CSA DEKRA Certification B.V.	C22.2 No. 158	1101145
UL UL International Germany GmbH	UL 1059	E45172

Downloads

Environmental Product Compliance

Compliance Search

Environmental Product
Compliance 711-402



Documentation

Additional Information

Technical Section

03.04.2019

pdf

2027.26 KB



CAD/CAE-Data

CAE data

EPLAN Data Portal
711-402



WSCAD Universe
711-402

