

**CLI MH 70 HSTR****Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com



CLI M identification markers are slid onto CLI MH carrier strips and secured by means of cable ties. The system is particularly suitable for large conductor and cable cross-sections.

**Advantages:**

- Combination marker for cable and pipe markers
- One size for all diameters above 16 mm<sup>2</sup>
- Unrestricted combination options
- Closed, permanently attached markers
- Very good legibility

**General ordering data**

Version	CableLine, Accessories, 10 - 317 mm, 70 x 11.3 mm, black
Order No.	<a href="#">0524400000</a>
Type	CLI MH 70 HSTR
GTIN (EAN)	4008190075057
Qty.	100 pc(s).

## CLI MH 70 HSTR

Weidmüller Interfaces GmbH &amp; Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	3 mm	Depth (inches)	0.118 inch
Height	70 mm	Height (inches)	2.756 inch
Width	11.3 mm	Width (inches)	0.445 inch
Net weight	0.81 g		

## Temperatures

Operating temperature range	-30...100 °C
-----------------------------	--------------

## General data

Colour	black	Material	Polyamide 66
Material colour according to resistance code	0	Number of markers per combination	1 Component part = Accessories
Operating temperature range	-30...100 °C	Operating temperature range, max.	100 °C
Operating temperature range, min.	-30 °C	Recommended industries	Process, Machinery
Type of printing	neutral	UL 94 flammability rating	V-0
Version	halogen-free	Width	11.3 mm

## Conductor and cable markers

Conductor O.D.	10 - 317 mm	Conductor O.D., max.	317 mm
Conductor O.D., min.	10 mm	Conductor cross-section, max.	500 mm <sup>2</sup>
Conductor cross-section, min.	16 mm <sup>2</sup>	Cross-section for connected wire	16 - 500 mm <sup>2</sup>

## Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ECLASS 9.0	27-40-04-01
ECLASS 9.1	27-40-06-29	ECLASS 10.0	27-40-04-01
ECLASS 11.0	27-28-11-02	ECLASS 12.0	27-28-11-02

## Approvals

ROHS	Conform
------	---------

## Downloads

Engineering Data	<a href="#">WSCAD</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

**CLI MH 70 HSTR**

**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

[info@weidmueller.com](mailto:info@weidmueller.com)

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

**Example of use**

