

**Industrial Ethernet
IE-BHS-V14M-RJA**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



PushPull plug-in connector according to IEC
61076-3-117 var.14 (PROFINET) in metal, empty
enclosure for hybrid plug-in connectors

General ordering data

Type	IE-BHS-V14M-RJA
Order No.	1011540000
Version	Empty enclosure
GTIN (EAN)	4032248718689
Qty.	10 pc(s).

Creation date August 22, 2020 3:38:00 AM CEST

Catalogue status 14.08.2020 / We reserve the right to make technical changes.

Data sheet

Industrial Ethernet IE-BHS-V14M-RJA

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Width	22.2	Width (inches)	0.874 inch
Height	42 mm	Height (inches)	1.654 inch
Depth	34.7 mm	Depth (inches)	1.366 inch
Net weight	20.49 g		

Temperatures

Operating temperature, max.	70 °C	Operating temperature, min.	-40 °C
Operating temperature	-40 °C...70 °C		

General data

Colour		Configuration	Plug housing with labelling tag holder: 9*11 mm; suitable for holding RJ45 and fibre-optic inserts
	Miscellaneous		
Housing main material	Zinc diecast	Plugging cycles	750
Protection degree	IP67	Seal material	EPDM

General standards

Certificate no. (cULus)	E316369	Connector standard	IEC 61076-3-117 Var. 14
-------------------------	---------	--------------------	-------------------------

Classifications

ETIM 6.0	EC001031	ETIM 7.0	EC001031
eClass 9.0	27-18-27-02	eClass 9.1	27-18-27-02
eClass 10.0	27-18-27-02	UNSPSC	30-21-18-01

Approvals

Approvals



ROHS Conform

Downloads

Approval/Certificate/Document of Conformity	DUXR.E316369 PROFINET Manufacturer's Declaration
Brochure/Catalogue	CAT 9 IETH 18/19 EN FL FIELDWIRING EN PI PROFINET CABLING EN
Engineering Data	WSCAD
Engineering Data	STEP
User Documentation	MAN IE GUIDE DE MAN IE GUIDE EN Designation key / Type key

Data sheet**Industrial Ethernet
IE-BHS-V14M-RJA**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings**Installation cut-out**