

**THM  
THM GEW 15/6 WS**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



THM GEW woven-fabric labels are made from a very flexible cotton fabric. Delivery on reels for use with thermal transfer printers enables an adhesive layer which is thicker than that of A4 sheets for office laser printers. Together, this flexibility and the thick adhesive layer ensure higher adhesive strength and enable use on angular or round objects such as e.g. cables or hoses.

**General ordering data**

Type	THM GEW 15/6 WS
Order No.	<a href="#">1059780000</a>
Version	THM, Device markers, 15 x 6 mm, White
GTIN (EAN)	4032248808175
Qty.	1 pc(s).
compatible printer	<a href="#">2430920000</a> <a href="#">2448870000</a>

**THM  
THM GEW 15/6 WS**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**
**Dimensions and weights**

Width	6 mm	Width (inches)	0.236 inch
Height	15 mm	Height (inches)	0.591 inch
Depth	0.3 mm	Depth (inches)	0.012 inch
Net weight	384 g		

**General data**

Adhesive	Natural rubber adhesive	Approval acc. to UL 969	No
Colour	White	Material	Cotton fabric
Material colour according to resistance code	9	Number per roll	10,000
Number per sheet	10,000	Operating temperature range	-29...80 °C
Printing method	Thermotransfer	UL 94 flammability rating	V-0
Version	Self-adhesive	Width	6 mm

**Classifications**

ETIM 3.0	EC001288	ETIM 4.0	EC001288
ETIM 5.0	EC001288	ETIM 6.0	EC001288
UNSPSC	55-12-16-00	eClass 5.1	27-14-91-29
eClass 6.2	27-14-91-29	eClass 7.1	27-14-91-29
eClass 8.1	27-14-91-03	eClass 9.0	27-40-06-29
eClass 9.1	27-40-06-29		

**Approvals**

ROHS	Conform
------	---------

**Downloads**


Engineering Data	<a href="#">EPLAN, WSCAD</a>
Software	<a href="#">M-Print PRO configuration file</a>

**Data sheet**

**THM  
THM GEW 15/6 WS**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**



**Data sheet**

**THM  
THM GEW 15/6 WS**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

