

**P-series  
TW PRV16 1-16**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com


**DCS marshalling**

Our innovative PRV terminal blocks for DCS marshalling featuring a PUSH IN connection and our multifunctional DCS marshalling terminals featuring a screw connection (WMF) not only save space in the panel; they also guarantee more effective signal transmission in process control systems.

**General ordering data**

Type	TW PRV16 1-16
Order No.	<a href="#">1230120000</a>
Version	P-series, Separation plate, Grey, 2 mm, Printed 1-16, horizontal
GTIN (EAN)	4050118013924
Qty.	10 pc(s).

**P-series  
TW PRV16 1-16**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**
**Dimensions and weights**

Width	2 mm	Width (inches)	0.079 inch
Height	225 mm	Height (inches)	8.858 inch
Depth	100 mm	Depth (inches)	3.937 inch
Net weight	26.4 g		

**Temperatures**

Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	125 °C
----------------------------------	--------	----------------------------------	--------

**Material data**

Material	Polycarbonate	Colour	Grey
UL 94 flammability rating	V-0		

**System specifications**

Version	Printed 1-16, horizontal	Number of levels	16
Mounting rail	none		

**Additional technical data**

Snap-on	Yes
---------	-----

**Classifications**

ETIM 3.0	EC000886	ETIM 4.0	EC000886
ETIM 5.0	EC000886	ETIM 6.0	EC000886
eClass 6.2	27-14-11-20	eClass 7.1	27-14-11-20
eClass 8.1	27-14-11-33	eClass 9.0	27-14-11-33
eClass 9.1	27-14-11-33		

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Brochure/Catalogue	<a href="#">CAT 1 TERM 16/17 EN</a>
Engineering Data	<a href="#">EPLAN, WSCAD, Zuken E3.S</a>

**Data sheet**

**P-series  
TW PRV16 1-16**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

