

**cable lug, terminal end  
KWN-M6/-4 90**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



**The use of insulated connectors guarantees users consistent electrical connection quality in the long term.**

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

**General ordering data**

Type	KWN-M6/-4 90
Order No.	<a href="#">1495320000</a>
Version	cable lug, terminal end, 4 mm <sup>2</sup>
GTIN (EAN)	4050118304763
Qty.	100 pc(s).

## Data sheet

### cable lug, terminal end KWN-M6/-4 90

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technical data

### Dimensions and weights

Weight	0.29 g	Net weight	2.84 g
--------	--------	------------	--------

### Technical data

Version	Euro series 90°
---------	-----------------

### Connectors

Conductor cross-section	4 mm <sup>2</sup>	Connection length (l)	12.5 mm
Flange width (b)	11 mm	Hole	M 6
Inside diameter of flange (d2)	6.4 mm	Inside diameter of shaft (d1)	3 mm
Insulation	not available	Outside diameter of shaft (d3)	5 mm
Shaft length (a)	7 mm		

### Classifications

ETIM 3.0	EC001509	ETIM 4.0	EC001509
ETIM 5.0	EC001051	ETIM 6.0	EC001051
eClass 6.2	27-40-02-05	eClass 7.1	27-40-02-04
eClass 8.1	27-40-02-05	eClass 9.0	27-40-02-05
eClass 9.1	27-40-02-05		

### Approvals

ROHS	Conform
------	---------

### Downloads

Brochure/Catalogue	<a href="#">CAT 6 TOOLS 15/16 EN</a>
--------------------	--------------------------------------

**Data sheet****cable lug, terminal end  
KWN-M6/-4 90**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**