



#### General ordering data

Order No.	1737150000
Part designation	VP M20-EXE MS
Version	Blanking plug, Brass, nickel-plated, External thread: M 20 x 1.5, IP 66, IP 68
EAN	4008190956622
Qty.	50 pc(s).

#### General details

AF size 1	23 mm
Assembly temperature, max.	100 °C
Assembly temperature, min.	-40 °C
Class of protection with thread gasket	IP 66, IP 68
External thread	M 20 x 1.5
Length	18 mm
Length of thread	15 mm
Material	Brass, nickel-plated
Protection class	IP 66, IP 68
Sealing	NBR
Type of cable gland	metric

#### Approvals

Approvals institutes	н.ä.
----------------------	------

#### Classifications

ETIM 2.0	EC000032
ETIM 3.0	EC000032
eClass 4.1	27-14-12-10
eClass 5.0	27-14-91-10
eClass 5.1	27-14-91-10

#### Similar products

Order No.	Part designation	Version
1737140000	VP M16-EXE MS	Blanking plug, Brass, nickel-plated, External thread: M 16 x 1.5, IP 66, IP 68
1737160000	VP M25-EXE MS	Blanking plug, Brass, nickel-plated, External thread: M 25 x 1.5, IP 66, IP 68
1737170000	VP M32-EXE MS	Blanking plug, Brass, nickel-plated, External thread: M 32 x 1.5, IP 66, IP 68
1737180000	VP M40-EXE MS	Blanking plug, Brass, nickel-plated, External thread: M 40 x 1.5, IP 66, IP 68
1737190000	VP M50-EXE MS	Blanking plug, Brass, nickel-plated, External thread: M 50 x 1.5, IP 66, IP 68
1737200000	VP M63-EXE MS	Blanking plug, Brass, nickel-plated, External thread: M 63 x 1.5, IP 66, IP 68
1719360000	VP 11-EXE MS	Blanking plug, Brass, nickel-plated, External thread: PG 11, IP 66, IP 68
1719370000	VP 13,5-EXE MS	Blanking plug, Brass, nickel-plated, External thread: PG 13.5, IP 66, IP 68
1719380000	VP 16-EXE MS	Blanking plug, Brass, nickel-plated, External thread: PG 16, IP 66, IP 68
1719390000	VP 21-EXE MS	Blanking plug, Brass, nickel-plated, External thread: PG 21, IP 66, IP 68
1719400000	VP 29-EXE MS	Blanking plug, Brass, nickel-plated, External thread: PG 29, IP 66, IP 68
1719430000	VP 48-EXE MS	Blanking plug, Brass, nickel-plated, External thread: PG 48, IP 66, IP 68
1719340000	VP 7-EXE MS	Blanking plug, Brass, nickel-plated, External thread: PG 7, IP 66, IP 68
1719350000	VP 9-EXE MS	Blanking plug, Brass, nickel-plated, External thread: PG 9, IP 66, IP 68