

**Clamping yoke
KLBUE CO 4**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Product image**Shielding and earthing**

Our protective earth conductor and shielding terminals featuring different connection technologies allow you to effectively protect both people and equipment from interference, such as electrical or magnetic fields. A comprehensive range of accessories rounds off our range.

General ordering data

Type	KLBUE CO 4
Order No.	1749161001
Version	Clamping yoke, Clamping yoke, Steel
GTIN (EAN)	4032248064458
Qty.	10 pc(s).

**Clamping yoke
KLBUE CO 4**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data**Dimensions and weights**

Width	25 mm	Width (inches)	0.984 inch
Height	32 mm	Height (inches)	1.26 inch
Depth	56 mm	Depth (inches)	2.205 inch
Mounting dimension - width	31 mm	Net weight	53.252 g

Temperatures

Storage temperature, max.	40 °C	Storage temperature, min.	10 °C
Storage temperature	10 °C...40 °C		

Material data

Material	Steel	Colour	silver
----------	-------	--------	--------

System specifications

Version	For a shield connection
---------	-------------------------

Additional technical data

Explosion-tested version	No	Installation advice	Busbar
Type of fixing	Snap-on		

Conductors for clamping (rated connection)

Cable diameter, max.	28 mm	Cable diameter, min.	15 mm
----------------------	-------	----------------------	-------

Dimensions

Pitch in mm (P)	25 mm
-----------------	-------

Classifications

ETIM 6.0	EC002020	ETIM 7.0	EC002020
eClass 9.0	27-14-11-50	eClass 9.1	27-14-11-50
eClass 10.0	27-14-11-50	UNSPSC	30-21-18-01

Approvals

Approvals



ROHS Conform

Downloads

Brochure/Catalogue	CAT 1 TERM 16/17 EN
Engineering Data	EPLAN, WSCAD
Engineering Data	STEP
User Documentation	Beipackzettel_KLBUE.pdf StorageConditionsTerminalBlocks

Creation date April 26, 2020 11:49:49 AM CEST

Catalogue status 17.04.2020 / We reserve the right to make technical changes.