

**Industrial Ethernet
IE-BH-V01M**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Bayonet plug-in connectors according to IEC
61076-3-106 ver.1 (EtherNet/IP), metal, empty housing

General ordering data

Type	IE-BH-V01M
Order No.	1963540000
Version	Empty enclosure, Flange-mounted housing, Variant 1 to IEC 61076-3-106, IP67
GTIN (EAN)	4032248645633
Qty.	10 pc(s).

Creation date August 16, 2020 10:56:01 AM CEST

Catalogue status 24.07.2020 / We reserve the right to make technical changes.

Industrial Ethernet IE-BH-V01M

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Width	32	Width (inches)	1.26 inch
Height	32 mm	Height (inches)	1.26 inch
Depth	23.5 mm	Depth (inches)	0.925 inch
Net weight	46.6 g		

Temperatures

Operating temperature, max.	70 °C	Operating temperature, min.	-40 °C
Operating temperature	-40 °C...70 °C		

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

General data

Colour	Miscellaneous	Housing main material	Zinc diecast
Plugging cycles	750	Protection degree	IP67
Seal material	EPDM	Type of mounting	4 screws, Central nut

General standards

Connector standard	IEC 61076-3-106 Var. 1
--------------------	------------------------

Classifications

ETIM 6.0	EC001031	ETIM 7.0	EC001031
eClass 9.0	27-18-27-02	eClass 9.1	27-18-27-02
eClass 10.0	27-18-27-02	UNSPSC	30-21-18-17

Approvals


ROHS	Conform
------	---------

Downloads

Approval/Certificate/Document of Conformity	GOST Approval DUXR.E316369
Brochure/Catalogue	CAT 9 IETH 18/19 EN MB FREECONTACT EN FL FIELDWIRING EN PI PROFINET CABLING EN
Engineering Data	WSCAD
Product Change Notification	Technical change to Bulkhead Variant 1 (Metal) - EN Technical change to Bulkhead Variant 1 (Metal) - DE
User Documentation	MAN IE GUIDE DE MAN IE GUIDE EN Designation key / Type key Manual

**Industrial Ethernet
IE-BH-V01M**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings**Installation cut-out**

Mounting cut-out: 1. With central screw connection / 2. For mounting with four M3 screws