

**Accessories**  
**MOFU 15/35 ZDUB****Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com**Product image****Spring connection with tension clamp Technology**

Tension clamp technology is a universal contact system for all common conductor connection types. Its fantastic level of flexibility makes the tension clamp a profitable alternative connection.

**General ordering data**

Type	MOFU 15/35 ZDUB
Order No.	<a href="#">1723660000</a>
Version	Accessories, Mounting foot
GTIN (EAN)	4008 1909 7553 1
Qty.	50 pc(s).

**Accessories**  
**MOFU 15/35 ZDUB**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data****Dimensions and weights**

Width	5 mm	Width (inches)	0.197 inch
Height	43 mm	Height (inches)	1.693 inch
Depth	15 mm	Depth (inches)	0.591 inch
Net weight	1.216 g		

**Temperatures**

Storage temperature, max.	40 °C	Storage temperature, min.	10 °C
Storage temperature	10 °C...40 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	120 °C		

**Material data**

Material	Wemid	Colour	dark beige
UL 94 flammability rating	V-0		

**System specifications**

Version	For the mounting rails	End cover plate required	Yes
Rail	TS 35, TS 15		

**Additional technical data**

Explosion-tested version	No	Open sides	right
Type of fixing	Snap-on	Type of mounting	Plugged

**Conductors for clamping (rated connection)**

Connection direction	top	Type of connection	Tension-clamp connection
----------------------	-----	--------------------	--------------------------

**Dimensions**

Pitch in mm (P)	18 mm	TS 15 offset	21 mm
TS 35 offset	2 mm		

**Classifications**

ETIM 6.0	EC002848	ETIM 7.0	EC002848
eClass 9.0	27-14-11-92	eClass 9.1	27-14-11-92
eClass 10.0	27-14-11-92	UNSPSC	30-21-18-11

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Engineering Data	<a href="#">EPLAN, WSCAD, Zuken E3.S</a>
Engineering Data	<a href="#">26403_MOFU_15-35_ZDUB_DXF.dxf</a> <a href="#">STEP</a>
User Documentation	<a href="#">StorageConditionsTerminalBlocks</a>