

**Clamping yoke
BS 35II KLBUE HOLDER**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Product image**Shielding and earthing**

Our protective earth conductor and shielding terminals featuring different connection technologies allow you to effectively protect both people and equipment from interference, such as electrical or magnetic fields. A comprehensive range of accessories rounds off our range.

General ordering data

| | |
|------------|--------------------------------------|
| Type | BS 35II KLBUE HOLDER |
| Order No. | 1723800000 |
| Version | Clamping yoke, Set of fixings, Steel |
| GTIN (EAN) | 4008 190377038 |
| Qty. | 10 pc(s). |

**Clamping yoke
BS 35II KLBUE HOLDER**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Dimensions and weights

| | | | |
|------------|---------|-----------------|------------|
| Height | 35 mm | Height (inches) | 1.378 inch |
| Depth | 36.5 mm | Depth (inches) | 1.437 inch |
| Net weight | 38.5 g | Diameter | 3 mm |

Temperatures

| | | | |
|---------------------------|----------------|---------------------------|--------|
| Storage temperature, max. | 55 °C | Storage temperature, min. | -25 °C |
| Storage temperature | -25 °C...55 °C | | |

Material data

| | | | |
|----------|-------|--------|--------|
| Material | Steel | Colour | silver |
|----------|-------|--------|--------|

System specifications

| | | | |
|---------|---------------|------|-------|
| Version | Clamping yoke | Rail | TS 35 |
|---------|---------------|------|-------|

Additional technical data

| | | | |
|--------------------------|-----------------|---------------------|-----------------|
| Explosion-tested version | Yes | Installation advice | Direct mounting |
| Type of fixing | when screwed in | | |

Dimensions

| | | | |
|----------|------|--------------|---------|
| Diameter | 3 mm | TS 35 offset | 26.5 mm |
|----------|------|--------------|---------|

Classifications

| | | | |
|-------------|-------------|------------|-------------|
| ETIM 6.0 | EC002848 | ETIM 7.0 | EC002848 |
| eClass 9.0 | 27-14-11-92 | eClass 9.1 | 27-14-11-92 |
| eClass 10.0 | 27-14-11-92 | UNSPSC | 30-21-18-11 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|--------------------|---|
| Brochure/Catalogue | CAT 1 TERM 16/17 EN |
| Engineering Data | EPLAN, WSCAD |
| Engineering Data | STEP |
| User Documentation | StorageConditionsTerminalBlocks |