

**SKMU PA (plastic locknut)  
SKMU M63 K SW**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



Weidmüller has a variety of different cable and wire entry systems in the Portfolio: with different designs of plastic, brass and stainless steel cable glands in the IP66, 67, 68 or IP69k protection classes. As a complete alternative to cable glands, pre-assembled cables with modular multi-wire or multi-cable entry systems can be simply and quickly inserted into electrical equipment. Last but not least, Weidmüller offers EX-certified cable glands and cable/wire entry systems.

- Cable glands made from plastic and brass
- EMC screwed joints
- for areas at risk of explosion
- VDE, CSA and UL approvals

**General ordering data**

Type	SKMU M63 K SW
Order No.	<a href="#">1736980000</a>
Version	SKMU PA (plastic locknut), Locknut, M 63, 8 mm, Polyamid 6 (PA6 - GF30)
GTIN (EAN)	4008 190956455
Qty.	5 pc(s).

## Data sheet

### SKMU PA (plastic locknut) SKMU M63 K SW

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

## Technical data

### Dimensions and weights

Net weight 20.4 g

### General information

Material	Polyamid 6 (PA6 - GF30)	Cable glands	metric
External thread	M 63	Pitch of thread	1.5 mm
Length of thread	8 mm	AF size 1	75 mm
Operating temperature range, min.	-40 °C	Operating temperature range, max.	100 °C
Thickness	8 mm	UL 94 flammability rating	V-2
Internal thread	M 63	Halogen	No

### Classifications

ETIM 6.0	EC000940	ETIM 7.0	EC000940
eClass 9.0	27-14-44-24	eClass 9.1	27-14-44-24
eClass 10.0	27-14-44-24	UNSPSC	30-21-18-01

### Approvals

Approvals



ROHS Conform

### Downloads

Brochure/Catalogue	<a href="#">CAT 5 ENCL 17/18 EN</a>
Engineering Data	<a href="#">EPLAN, WSCAD</a>
Engineering Data	<a href="#">STEP</a>

**Data sheet**

**SKMU PA (plastic locknut)**  
**SKMU M63 K SW**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

