

**W-Series
WQV 50N/4**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Product image**Klippon® Connect with clamping yoke Technology**

The high reliability and variety of designs of the terminal blocks with clamping yoke connections make planning easier and optimises operational safety. Klippon® Connect provides a proven response to a range of different requirements.

General ordering data

Type	WQV 50N/4
Order No.	1834080000
Version	W-Series, Cross-connector, For the terminals, Number of poles: 4
GTIN (EAN)	4032248379873
Qty.	5 pc(s).

Creation date August 18, 2020 8:36:32 AM CEST

Catalogue status 14.08.2020 / We reserve the right to make technical changes.

W-Series
WQV 50N/4

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data**Dimensions and weights**

Width	9.5 mm	Width (inches)	0.374 inch
Height	65.5 mm	Height (inches)	2.579 inch
Depth	17.5 mm	Depth (inches)	0.689 inch
Net weight	48 g		

Temperatures

Storage temperature, max.	55 °C	Storage temperature, min.	-25 °C
Storage temperature	-25 °C...55 °C		

Material data

Material	tinned copper	Colour	Silver grey
----------	---------------	--------	-------------

System specifications

Version	For the terminals
---------	-------------------

Additional technical data

Installation advice	Direct mounting	Type of fixing	when screwed in
---------------------	-----------------	----------------	-----------------

Cross-connector

Number of cross-connected terminals	4	Rated current, multi-pole	150 A
Type	Cross-connector		

Dimensions

Pitch in mm (P)	18.5 mm
-----------------	---------

Rating data

Rated current	150 A
---------------	-------

Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
eClass 9.0	27-14-11-40	eClass 9.1	27-14-11-40
eClass 10.0	27-14-11-40	UNSPSC	30-21-18-01

Approvals

Approvals



ROHS	Conform
------	---------

Data sheet**W-Series
WQV 50N/4**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data**Downloads**

Approval/Certificate/Document of Conformity	EAC certificate
Brochure/Catalogue	CAT 1 TERM 16/17 EN
Engineering Data	EPLAN, WSCAD, Zuken E3.S
Engineering Data	STEP
User Documentation	StorageConditionsTerminalBlocks Instruction
