

**cable lug, terminal end  
LIS 2,5M5 V**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Insulated forked-cable connector made from PVC  
or PC/PA**

- Conventional designs
- Not soldered
- With conical entry funnel

**General ordering data**

Type	LIS 2,5M5 V
Order No.	<a href="#">9200380000</a>
Version	cable lug, terminal end, Insulated cable connector, 1.5 mm <sup>2</sup> - 2.5 mm <sup>2</sup> , blue
GTIN (EAN)	40322484 10224
Qty.	100 pc(s).

Creation date April 21, 2020 2:32:29 PM CEST

Catalogue status 17.04.2020 / We reserve the right to make technical changes.

**cable lug, terminal end  
LIS 2,5M5 V**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data****Dimensions and weights**

Width	22.9 mm	Width (inches)	0.902 inch
Depth	6.1 mm	Depth (inches)	0.24 inch
Net weight	0.78 g		

**Connectors**

Conductor cross-section, max.	2.5 mm <sup>2</sup>	Conductor cross-section, min.	1.5 mm <sup>2</sup>
Connection density (S1)	0.8 mm	Connection length (l)	17.8 mm
Dimension	M 5	Dimension (bolt)	M 5
Identification colour	blue	Inside diameter (d1)	5.3 mm
Insulation	Available	Material/plastic	PVC
Outside diameter (d)	8.1 mm	Plastic collar diameter (D)	4.5 mm
Plastic collar length (b)	11.3 mm		

**Classifications**

ETIM 6.0	EC001059	ETIM 7.0	EC001059
eClass 9.0	27-40-02-92	eClass 9.1	27-40-02-12
eClass 10.0	27-40-02-92	UNSPSC	41-11-36-37

**Approvals**

Approvals



ROHS Conform

**Downloads**

Brochure/Catalogue	<a href="#">CAT 6 TOOLS 15/16 EN</a>
Engineering Data	<a href="#">EPLAN</a>

**Data sheet****cable lug, terminal end  
LIS 2,5M5 V**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**