

- ×
- [Products](#)
 - [Industry Solutions](#)
 - [CAREERS](#)
 - [Resources](#)
 - [Find Distributor](#)
 - [Contact Molex](#)

Enter Part No. or Keyw

 [Product Name Index](#)

 [Cross Reference](#)



Part Number: 130144-0081

Safeway Hospital Duty Connector, 2 Pole/3 Wire, NEMA 5-15 , 125V, Yellow



Series image - Reference only

Status: Active
Series: [130144](#)
Category: Wiring Devices
Overview: [Heavy-Duty Industrial Wiring Devices](#)
Engineering/Old PN: 85269YL

Product Environmental Compliance

[EU ELV](#):Not Reviewed

[EU RoHS](#):Not Reviewed

[EU RoHS Phthalates](#):Not Reviewed

[China RoHS](#):Not Reviewed

[REACH SVHC](#):Not Reviewed

[Low-Halogen Status](#):Not Reviewed

Part Detail

General

Status	Active
Category	Wiring Devices
Series	130144
IP Rating	N/A
NEMA Configuration	NEMA 5-15
Overview	Heavy-Duty Industrial Wiring Devices
Product Literature Order No	987650-8068
Product Name	Safeway
Receptacle Type	Single
Specialty	Hospital Duty
Type	Connector
UPC	78678894287

Physical

Flange	No
Flip Lid	No
Gender	Female
Length	N/A
Locking Blade	No

Poles 2-pole/3-wire
Electrical

(Please review the Product Specification for specific details.)

Cord Type	N/A
Current - Maximum per Contact	15.0A
GFCI	No
Lighted Connector	No
Voltage - Maximum	125V
Agency Certification	

Please find UL Certificates by searching the UL Database using the Molex Series Number. [Click here to visit the UL Database](#)

CSA LR6837
Material Info

Engineering Number 85269YL

Application Tooling

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling

[Check our list of old tooling that used to be available for this part](#)

Products+

- [Product Categories](#)
- [Product Index](#)
- [Industries](#)

Quick Links+

- [Company Information](#)
- [Contact Molex](#)
- [Cross-Reference](#)
- [Koch Industries](#)
- [Investor Relations](#)
- [Literature](#)
- [Press Room / Press Releases](#)
- [Sitemap](#)
- [Terms & Conditions](#)

Resources+

- [Supply Chain Transparency](#)
- [Business Continuity](#)
- [Compliance](#)
- [ecocare](#)
- [Feedback | Help](#)
- [Jobs](#)
- [Legal | Trademarks](#)
- [Supplier Portal](#)
- [Privacy Policy](#)
- [Tradeshows](#)

Stay Connected



Molex is a registered trademark of Molex, LLC in the United States of America and may be registered in other countries; all other trademarks listed herein belong to their respective owners.

© Copyright 2018