



**Part Number :** [1300850376](#)

**Product Description :** Woodhead POW-R-MATIC Heavy Duty Cable Reel with Retraction Weight of 7lbs., 8/4 Type W, 18.29m (60.0') Cord Length with Flying Leads

**Series Number :** 130085

**Status :** Active

**Product Category :** Electrical Reels

**Engineering Number :** 92745



---

## Documents & Resources

---

### Product Environment Compliance

#### Compliance

|                    |              |
|--------------------|--------------|
| China RoHS         | Not Reviewed |
| EU ELV             | Not Reviewed |
| Low-Halogen Status | Not Reviewed |
| REACH SVHC         | Not Reviewed |
| EU RoHS            | Not Reviewed |

#### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

#### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

#### Additional Product Compliance Information

---

## Part Details

### General

|                    |                                                                                                                                      |
|--------------------|--------------------------------------------------------------------------------------------------------------------------------------|
| Status             | Active                                                                                                                               |
| Category           | Electrical Reels                                                                                                                     |
| Series             | 130085                                                                                                                               |
| Description        | Woodhead POW-R-MATIC Heavy Duty Cable Reel with Retraction Weight of 7lbs., 8/4 Type W, 18.29m (60.0') Cord Length with Flying Leads |
| Comments           | Applications: Vertical Lift, Drag, Recovery and Horizontal Stretch with 10% Sag.                                                     |
| Enclosure Rating   | NEMA 3R                                                                                                                              |
| NEMA Configuration | N/A                                                                                                                                  |
| Product Name       | POW-R-MATIC                                                                                                                          |
| Type               | Cable Reel                                                                                                                           |
| UPC                | 78678879366                                                                                                                          |

### Agency

|     |         |
|-----|---------|
| CSA | LR29921 |
|-----|---------|

### Electrical

|                               |       |
|-------------------------------|-------|
| Current - Maximum per Contact | 32.0A |
| GFCI                          | No    |
| Lamp Wattage - Maximum        | N/A   |
| On/Off Switch                 | N/A   |
| Voltage - Maximum             | 600V  |

### Physical

|                |                 |
|----------------|-----------------|
| Bulb Included  | N/A             |
| Cable Length   | N/A             |
| Cable Movement | Ratchet Lock    |
| Cord Length    | 18.29m (60.0')  |
| Cord Type      | 8/4 Type W      |
| Depth          | 0.58m (22.750") |

|                          |                   |
|--------------------------|-------------------|
| Drum Lock                | Ratchet           |
| Duty                     | Heavy             |
| Guide Arm                | Option Available  |
| Height                   | 0.59m (23.38")    |
| Lamp Type                | N/A               |
| Material - Coating       | Powder Coating    |
| Material - Housing       | Steel             |
| Mounting Style           | Rigid             |
| Number of Conductors     | 4                 |
| Packaging Type           | Carton            |
| Primary Cord/Cable Entry | 1" NPT            |
| Retraction Weight        | 3.2kg (7.0 lb)    |
| Width                    | 577.90mm (22.75") |
| Wire Size (AWG)          | 8                 |