



ACM Series

**PREMIUM WHOLE HOUSE AIR CLEANING SOLUTION
4" MEDIA AIR CLEANER**

FEATURES

- Slim profile for easy installation and easy stocking.
- Heavy-duty, 20 gauge galvanized steel cabinet construction – assembles using toggle locks.
- Factory-punched screw and drill-access holes in cabinet for fast and simple installation.
- Snap-on, ABS plastic cabinet door for easy filter replacement without tools.
- Private label program available

| Model Number | CFM | Nominal Size | Cabinet Dimensions | Recommended CFM Range | Shipping Weight |
|---------------------|------|--------------|---|-----------------------|-----------------|
| ACM1000M-108 | 1000 | 16" x 20" | 18 ¹ / ₈ " H x 19 ⁷ / ₈ " W x 5 ¹ / ₂ " D | 600-1200 | 14 lbs. |
| ACM1400M-108 | 1400 | 16" x 25" | 18 ¹ / ₈ " H x 24 ⁷ / ₈ " W x 5 ¹ / ₂ " D | 1000-1600 | 15.75 lbs. |
| ACM1600M-108 | 1600 | 20" x 20" | 22 ¹ / ₄ " H x 19 ⁷ / ₈ " W x 5 ¹ / ₂ " D | 1200-1800 | 15 lbs. |
| ACM2000M-108 | 2000 | 20" x 25" | 22 ¹ / ₄ " H x 24 ⁷ / ₈ " W x 5 ¹ / ₂ " D | 1600-2200 | 17.25 lbs. |

Each ACM includes a MERV 8 media filter.
Shipping specifications meets National Safety Transit Test (NSTT) standards.


FILTER REPLACEMENTS FOR 4" MEDIA AIR CLEANERS

FEATURES

- Available in MERV 8 and MERV 11 ratings.
- Includes installation arrow to indicate airflow direction.

STANDARD MERV 8 FILTER REPLACEMENT OR UPGRADE TO A PREMIUM MERV 11 FILTER

| Model Number | Rating | CFM | Nominal Size | Actual Filter Size | Shipping Weight |
|--------------------|---------|------|----------------|---|-----------------|
| FR1000M-108 | MERV 8 | 1000 | 16" x 20" x 4" | 15 ¹ / ₂ " H x 19 ¹ / ₂ " W x 3 ³ / ₄ " D | 4.5 lbs. |
| FR1000M-111 | MERV 11 | | | | 6 lbs. |
| FR1400M-108 | MERV 8 | 1400 | 16" x 25" x 4" | 15 ¹ / ₂ " H x 19 ¹ / ₂ " W x 3 ³ / ₄ " D | 6.25 lbs. |
| FR1400M-111 | MERV 11 | | | | 7 lbs. |
| FR1600M-108 | MERV 8 | 1600 | 20" x 20" x 4" | 19 ¹ / ₂ " H x 19 ¹ / ₂ " W x 3 ³ / ₄ " D | 5.5 lbs. |
| FR1600M-111 | MERV 11 | | | | 6.25 lbs. |
| FR2000M-108 | MERV 8 | 2000 | 20" x 25" x 4" | 19 ¹ / ₂ " H x 24 ¹ / ₂ " W x 3 ³ / ₄ " D | 7 lbs. |
| FR2000M-111 | MERV 11 | | | | 8 lbs. |



INDOOR AIR QUALITY / ZONING SYSTEMS

FILTER REPLACEMENTS FOR 5" MEDIA AIR CLEANERS

FEATURES

- Four standard sizes.
- MERV 8 media.

REPLACEMENT MEDIA FILTERS

| For Models | Model Number | CFM | Recommended CFM | A/C Tonnage | BTU Input Range |
|--------------------|-------------------|------|-----------------|-------------|-----------------|
| ACB1000-101 | FR1000-100 | 1000 | 600-1200 | up to 3.0 | up to 120,000 |
| ACB1400-101 | FR1400-100 | 1400 | 1000-1600 | up to 4.0 | up to 160,000 |
| ACB1600-101 | FR1600-100 | 1600 | 1200-1800 | up to 4.5 | up to 180,000 |
| ACB2000-101 | FR2000-100 | 2000 | 1600-2200 | up to 5.5 | up to 220,000 |



FR1400-100