


3-826629-6 Product Details

Share Print Email



3-826629-6

TE Internal Number: 3-826629-6

Active

View 3D PDF

.100 inch AMPMODU Headers

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Connector
- Header Type = Breakaway
- 36 Positions
- Mating Post Length = 6.70 mm
- 2.54 mm Centerline

View all Features

Quick Links

- Check Pricing & Availability
- Search for Tooling
- Product Feature Selector
- Contact Us About This Product

Documentation & Additional Information	
Product Drawings: - AMPMODU II STIFTLISTEN,EINREIHIG (PDF, English) Catalog Pages/Data Sheets: - None Available Product Specifications: - None Available Application Specifications: - None Available Instruction Sheets: - None Available CAD Files: (CAD Format & Compression Information) 2D Drawing (DXF, Version Y2) 3D Model (IGES, Version Y2) 3D Model (STEP, Version Y2)	Additional Information: - Product Line Information Related Products: - Tooling

List all Documents

Product Features (Please use the Product Drawing for all design activity)	
Product Type Features: - Product Type = Connector - Mount Angle = Vertical - PCB Mount Retention = Without - Surface Mount Compatible = No - Board Standoff = Without - Mounting Ears = Without - Mating Connector Lock = Without - Profile = Standard Mechanical Attachment: - Mating Post Length (mm [in]) = 6.70 [0.264] - Panel Mount Retention = Without Termination Features: - Termination Post Length (mm [in]) = 3.20 [0.126] - Solder Tail Contact Plating = Tin Body Features: - Header Type = Breakaway - Number of Positions = 36 - Centerline (mm [in]) = 2.54 [0.100] - Row-to-Row Spacing (mm [in]) = 2.54 [0.100] - Number of Rows = 1 - Selectively Loaded = No - Mount Type = Printed Circuit Board	Contact Features: - Contact Plating, Mating Area, Material = Gold (30) - Contact Base Material = Phosphor Bronze Housing Features: - Housing Material = Thermoplastic - GF - UL Flammability Rating = UL 94V-0 Industry Standards: - RoHS/ELV Compliance = RoHS compliant, ELV compliant - Lead Free Solder Processes = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C - RoHS/ELV Compliance History = Always was RoHS compliant Conditions for Usage: - High Temperature Housing = No Operation/Application: - High Speed Serial Data Connector = No Other: - Brand = AMP

Corporate Information Who We Are Investors News Room Supplier Portal Careers	Quick Links Check Distributor Inventory Cross Reference Find Documents & Drawings Product Compliance Support Center Site Map	Customer Support Email or Chat With Us Find a Phone Number Search Knowledge Base Manage your Account	Keep Me Informed Receive TE News, Events & Technology Updates Enter your email address Twitter Facebook LinkedIn YouTube Mobile App
---	---	--	---