

1

2

3

4


5

6

7

SIGN	DATE	DESCRIPTION	APPROVER
△	11/01'05	Electrical standard changed.	Marvin
△	04/20'06	2p to 6p with wedge is changed.	Marvin
△	8/13'06	Added VDE standard	梁仁松
△	10/30'06	Part No. is changed	Marvin
△	07/09'10	The solid and Stranded wire are changed from16-26 to16-28	Chen Bo
△	07/09'10	Rrmove the CSA mark	Chen Bo
△	08/12'13	update the drawing	Chen Bo

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

2p to 6p with wedge,above7p
without wedge(including 7p)



TJ xx 11 x 3 xxxx G	△
02 2 CONTACTS	△
03 3 CONTACTS	△
... ..	△
24 24 CONTACTS	△
Color	△
0 Black (RAL9005)	△
2 Red (RAL3001/D)	△
3 Orange(RAL2011/P)	△
4 Yellow(RAL1018/A)	△
5 Green(RAL6018/T)	△
6 Blue (RAL5015/A)	△
8 Grey(RAL7035/D)	△
9 White(RAL1102)	△
△ C Green(RAL6018/U)	△
G RoHS compliant (lead<4%) In copper Alloy	△
0000 Standard @ Logo	△
000A Standard ANY Logo	△
0091 Standard ANY Logo	△
Any special item by customer request, please contact sales department.	△

Material

- Item a Clamp: Brass(CuZn) Ni plated
- Item b Terminal screw: Steel Zinc plating "--" slot type
- Item c Female contact: PhBz ,Tin plated
- Item d Terminal (housing): PA66 (UL94V-0)
- Item e Terminal cover:PA66 (UL94V-0)

△ △ △ Electrical cULus/VDE

- Voltage rating: 300VAC/300VAC
- Current rating: 10A/10.5A
- Wire range: 1.5mm²
- Solid wire(AWG): 16-28
- Stranded wire(AWG): 16-28
- Torque: 3Lb-In/0.2Nm
- Screw: M2
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV/2.5KV
- Operating temperature: -40°C to +115°C
- Safety Approval: cULus VDE
- Critical dimension: △



N = Number of poles

Dim A=Nx3.5

Dim B=(N-1)x3.5

Poles	Dim A	Dim B
2p-6p	±0.15	±0.15
7p-12p	±0.20	±0.20
13p-18p	±0.25	±0.25
19p-24p	±0.30	±0.30

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		TJ-3.5mm Series 2p-24p							
PART NO.		TJxx11x3xxxxG				DWG NO.		8TJ0501	
APPROVED		CHECKED	DESIGNED	DRAWN	CUST NO.				Tolerance
			Chen Bo 08/12`13	Chen Bo 08/12`13			UNIT: mm		X. ±0.50
							SCALE: NONE		X.X ±0.30
					SHEET: 01/01		REV: H		X.XX ±0.10
									X° ±1°

1

2

3

4

5

6

7