

Product Guide » ABB1SFA616921R2225

KA2-2225

[Print View..](#)
[Print to Pdf..](#)

General Information

Extended Product Type:	KA2-2225
Product ID:	1SFA616921R2225
EAN:	7320500201237
Catalog Description:	KA2-2225 LED bulb
Long Description:	LED bulb - White - Rated Voltage 230 V, AC - Rated Current 4 mA - Service Life 25 000 h



Categories

Products » Low Voltage Products and Systems » Control Products » Pilot Devices » Pilot Devices Accessories

Ordering

EAN:	7320500201237
Minimum Order Quantity:	20 piece
Customs Tariff Number:	85389099

Dimensions

Product Net Width:	0.010 m
Product Net Height:	0.010 m
Product Net Depth:	0.025 m
Product Net Weight:	0.004 kg

Container Information

Package Level 1 Units:	1 piece
Package Level 1 Width:	0.06 m
Package Level 1 Height:	0.01 m
Package Level 1 Length:	0.025 m
Package Level 1 Gross Weight:	0.004 kg
Package Level 2 Units:	20

Environmental

RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment
--------------	---

Additional Information

Accessory Type:	LED and filament bulbs
Color:	White
IIT Publishing Status:	Level 0 - Information enabled
Illumination:	Illuminated
Lamp Type:	LED
Luminance:	350 millicandela
Product Main Type:	KA2
Product Name:	LED bulb
Product Range:	Compact and Modular range
Product Type:	KA
Rated Current (I _n):	4 mA
Rated Operational Voltage:	230 V AC
RoHS Date:	0609 3
Service Life:	25000 hour(s)
Suitable For:	Choose the same colour for the LED and the lamp cap ore else use a clear lamp cap.
Wave Length:	x=0.31 y=3.2 nm

Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	1SFA1-3
RoHS Information:	1SFC151017D0202

Classifications

E-nummer:	8383626
ETIM 4.0:	EC002024 - Accessories for control circuit devices
ETIM 5.0:	EC002024 - Accessories for control circuit devices
Object Classification Code:	E
UNSPSC:	39121500

→ OK

☒ Products & Services only

+ Rate this page

+ Share this page

Your preferences:

Egypt

→ OK

English

→ OK

ABB contact for Egypt

Select another country

→ OK