




Amphenol's black plastic backshell accommodates most standard and high-density D-Subminiature connectors and is appropriate for most cable assemblies. This version is economical and highly durable. The split-grommet insert provides cable strain relief while making it easy to assemble.

**SPECIFICATIONS:**

Housing Material: Styrene (UL 94 VO)  
 Grommet Material: Polypropylene  
 Mounting Hardware: Steel, clear zinc finish

\*All materials are RoHS Compliant

**DIMENSIONS AND ORDERING INFORMATION**

| Shell Size | Standard # of Contacts | Hi-Density # of Contacts | Part #     | Dimensions       |                  |                  |                  |                  |                  | Cable Diameter Range |                  |
|------------|------------------------|--------------------------|------------|------------------|------------------|------------------|------------------|------------------|------------------|----------------------|------------------|
|            |                        |                          |            | A                | B                | C                | D                | E                | F                | Minimum              | Maximum          |
| E          | 9                      | 15                       | 17E-1724-1 | 1.217<br>(30.91) | 1.547<br>(39.29) | 0.640<br>(16.26) | 0.640<br>(16.26) | 0.400<br>(10.16) | 0.984<br>(24.99) | 0.210<br>(5.33)      | 0.350<br>(8.89)  |
| A          | 15                     | 26                       | 17E-1725-1 | 1.545<br>(39.24) | 1.505<br>(38.23) | 0.640<br>(16.26) | 0.640<br>(16.26) | 0.400<br>(10.16) | 1.312<br>(33.32) | 0.210<br>(5.33)      | 0.350<br>(8.89)  |
| B          | 25                     | 44                       | 17E-1726-1 | 2.090<br>(53.08) | 1.655<br>(42.04) | 0.710<br>(18.03) | 0.640<br>(16.26) | 0.522<br>(13.26) | 1.857<br>(47.17) | 0.230<br>(5.84)      | 0.450<br>(11.43) |
| C          | 37                     | 62                       | 17E-1727-1 | 2.734<br>(69.44) | 1.830<br>(46.48) | 0.906<br>(23.01) | 0.640<br>(16.26) | 0.726<br>(18.44) | 2.500<br>(63.50) | 0.350<br>(8.89)      | 0.640<br>(16.26) |
| D          | 50                     | 78                       | 17E-1728-1 | 2.645<br>(67.18) | 1.855<br>(47.12) | 0.940<br>(23.88) | 0.770<br>(19.56) | 0.726<br>(18.44) | 2.406<br>(61.11) | 0.350<br>(8.89)      | 0.640<br>(16.26) |