



REVISIONS			
SYM	ZONE	ECN, ERN NO.	DATE
B		PRODUCT DWG (EAR 14195)	JUN07/13
C		PRODUCT DWG (EAR 14206)	JUN19/13



FRONT VIEW




RECOMMENDED P.C.B. LAYOUT
(COMPONENT SIDE OF BOARD)
TOLERANCE: ±0.05mm


NOTES:

- MATERIALS:
HOUSING: HIGH TEMPERATURE PLASTIC, OR PBT
FLAMMABILITY UL94V-0.
CONTACTS: COPPER ALLOY,
PLATING: GOLD ON MATING AREA (SEE AMPHENOL PART NO. OPTION).
MATTE TIN OR GOLD FLASH ON CONTACT TAILS.
NICKEL UNDERPLATE.
SHELL: COPPER ALLOY,
NICKEL.


2. OPERATING TEMPERATURE: -40°C TO +105°C



TOP VIEW



SIDE VIEW



BOTTOM VIEW

AMPHENOL PART NO.: UE25-BEX5-10X

SERIES UE25=MINI USB RECEPTACLE MODIFIER
O=PBT
H=HIGH TEMP MATERIAL(<260°C)

TYPE B=SERIES B SHIELD OPTIONS
O=WITHOUT REAR SHELL

STYLE E=TOP ENTRY COLOUR
1=BLACK

CONTACT PLATING 5=30µ" [0.76 MICRONS] GOLD PLATING ON CONTACT MATING AREA NUMBER OF CONTACTS
5=5 CONTACTS

7=GOLD FLASH OVER NICKEL ON CONTACT MATING AREA.

UNLESS OTHERWISE SPECIFIED TOLERANCES ARE ±0.30mm	DRAWN <u>HUILAN WANG</u>	DATE <u>APR 25,08</u>	Amphenol Canada Corp.	
	DESIGNED <u>MT CHEN</u>	DATE <u>APR 25,08</u>		
	CHECKED <u>L.CHAN</u>	DATE <u>APR 25,08</u>	TITLE <u>UNIVERSAL SERIAL BUS MINI-B RECEPTACLE, VERTICAL PCB TAIL, RoHS COMPLIANT</u>	
	I. E. APPRD.			
	Q. A. APPRD.			
	DWG. APPRD. <u>K.LAMBIE TBD</u>		DWG <u>C</u>	DRAWING NO. <u>P-UE25-BEX5-10X</u>
	ENG. REL. NO.			REV. <u>C</u>
	REF.			
	DIMENSIONS ARE IN <u>MM [INCHES]</u>	CODE ID. NO. <u>03554</u>	SCALE <u>3/1</u>	WT. <u>-----</u>
			SURF. <u>-----</u>	SHEET <u>1</u> OF <u>1</u>

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING PURPOSES WITHOUT WRITTEN PERMISSION FROM AMPHENOL CANADA CORP.