




REV	DESCRIP	DATE	APPRVD





CONNECTOR WITH COVER OPENED



CONNECTOR WITH COVER OPENED




CONNECTOR WITH COVER CLOSED



CONNECTOR WITH COVER CLOSED

NOTES:




- MATERIAL:**
 - SHELL: ZINC ALLOY DIE CAST, 3 MICRONS [120 MICRO"] MIN NICKEL OVERALL.
 - COVER: ZINC ALLOY DIE CAST, 3 MICRONS [120 MICRO"] MIN NICKEL OVERALL.
 - SCREWS: STAINLESS STEEL.
 - HOUSING: HIGH TEMPERATURE THERMOPLASTIC, GLASS FILLED. FLAMMABILITY RATING UL94V-0, COLOR - BLACK.
 - CONTACTS: PHOSPHOR BRONZE, PLATING: 1.27 MICRONS [50 MICRO"] GOLD, OVER NICKEL ON MATING AREA, 2.54 MICRONS [100 MICRO"] TIN/LEAD ON SOLDER TAILS.
 - GASKETS: SILICONE RUBBER.
- OPERATING TEMPERATURE:** -40°C TO +105°C.
- ENVIRONMENT PERFORMANCE:** IP67.
- CONNECTOR IS ROHS COMPLIANT PER EU DIRECTIVE 2002/95/EC AND AMENDMENTS.**
- CONNECTOR IS ETHERNET CAT5 TEST COMPLIANT PER EIA-568-B STANDARD.**



UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETER TOLERANCES ARE:		APPROVALS	DATE	Amphenol Canada Corp.		
DECIMALS	ANGLES	DRAWN	OCT24/06			
.XX ± .10	± 1°	S.SEMENOV		TITLE		
.X ± .25		DESIGNED	OCT24/06			
MATERIAL AND FINISH		CHECKED		RJ RECEPTACLE		
REF.		QA APP'D				
CODE IDENT. NO.		IE APP'D		SIZE	DWG. NO.	REV.
		DWG APP'D	OCT24/06	C	P-ID450-000	1A
		A.GREEN		SCALE	PROJECT	SHEET
				1.75:1	ID	1 OF 2

DO NOT SCALE DRAWING
THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING PURPOSES WITHOUT PERMISSION FROM AMPHENOL CANADA CORP.

TABLE 1




PANEL CUTOUT

INDUSTRIAL CONNECTOR
PRODUCT NUMBERING SYSTEM

ID X1 X2 X3 - X4

ID	- Connector Designation
X1	- Style
4	- Receptacle assembly
5	- Plug assembly for RJ and power
6	- Plug assembly for USB, Fiber Optic, RF
7	- Plug and Receptacle assembly
X2	- Specials
5	- Standard
X3	- Interface discription
0	- RJ45
1	- USB
2	- Power
3	- Fiber optic
5	- RF
X4	- Specials
000	- Standard



UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN MILLIMETER
TOLERANCES ARE:

DECIMALS ANGLES
.XX ± .10 ± 1°
.X ± .25

MATERIAL AND FINISH

REF.

CODE IDENT. NO.

APPROVALS

DRAWN S.SEMENOV

DESIGNED S.SEMENOV

CHECKED

QA APP'D

IE APP'D

DWG APP'D A.GREEN

DATE

OCT24/06

OCT24/06

OCT24/06

Amphenol Canada Corp.

TITLE

RJ RECEPTACLE

SIZE C DWG. NO. P-ID450-000 REV. 1A

SCALE 1.5:1 PROJECT ID

SHEET 2 OF 2